

4 Port PCI RS232 Serial Adapter Card High Speed 16950 cable included

Produkt ID: PCI4S9503V



The PCI4S9503V 4 Port PCI RS232 Serial Adapter Card High Speed 16950 (cable included) lets you connect up to 4 RS-232 serial devices to the host computer at transfer rates up to 921 Kbps, and can be installed in either a 3.3V or 5V PCI/PCI-X slot.

The PCI Serial Card uses a 16 Byte buffer simultaneously in both transmit and receive channels, reducing the number of CPU interrupts while improving system performance.

Ideally suited to industrial applications, the buffered Serial PCI card is compatible with a broad range of operating systems, including Windows®, DOS®, Linux, and Unix environments.

Backed by a StarTech.com Lifetime warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet



Användning

- Connect multiple serial devices for a central serial device control system

- Perfect for Manufacturing applications such as CNC machinery, process control equipment, bar code scanners and serial printers
- Designed for use in critical applications with embedded systems and computer based machinery
- Data center applications for serial networking devices, high speed modems, monitoring equipment, long distance communication devices and printers
- Ideal for use in commercial and industrial applications such as POS networks, ATMs, and bank teller stations

Funktioner

- Adds four high speed RS-232 serial ports to your computer
- Works with both 3.3 volt and 5 volt PCI slots
- Breakout cable included
- Transfer rates of up to 921 Kbps
- PCI Bus Version 2.2 compliant

Hårdvara

Garantipolicy	Lifetime
Portar	4
Gränssnitt	Seriell
Busstyp	PCI / PCI-X (5 / 3.3V)
Korttyp	Standardprofil
Porttyp	Dongel (medföljer)
Industristandarder	RS232
Chipset-ID	PLX - PCI9030

Prestanda

Seriellt protokoll	RS-232
Maximal överföringshastighet	921,6 kbps

	FIFO	16 Bytes
Kontakt(er)		
	Kontakttyp(er)	1 - PCI/PCI-X (universell 3,3 & 5 V, 32-bitars)
	Externa portar	4 - DB-9 (9-stifts, D-Sub)
Mjukvara		
	OS-kompatibilitet	Windows® 8 (32bit), 7 (32), Vista(32), XP(32), 2000, NT, 98SE
		Linux & Unix SCO Open Server
Miljö		
	Drifttemperatur	0°C to 55°C (32°F to 131°F)
	Förvaringstemperatur	0°C to 65°C (32°F to 149°F)
	Luftfuktighet	5~85% RH
Utseende		
	Kabellängd	8.3 in [210 mm]
	Produktlängd	5.0 in [12.6 cm]
	Produkthöjd	3.9 in [10 cm]
Förpackning		
	Paketets längd	8.6 in [21.8 cm]
	Paketets bredd	2.2 in [56 mm]
	Paketets höjd	6.0 in [15.3 cm]
	Fraktvikt (förpackning)	1.0 lb [0.5 kg]
Vad det är i lådan		
	Ingår i paketet	1 - PCI Serial Card
		1 - 4 Port DB9 Break-out Cable
		1 - Driver CD
		1 - Instruction Manual

Warranty
Information

Warranty

Livslängd

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.