

4 Port PCI RS232 Serial Adapter Card High Speed 16950 cable included

Product ID: PCI4S9503V



The PCI4S9503V 4 Port PCI RS232 Serial Adapter Card High Speed 16950 (cable included) lets you connect up to 4 RS-232 serial devices to the host computer at transfer rates up to 921 Kbps, and can be installed in either a 3.3V or 5V PCI/PCI-X slot.

The PCI Serial Card uses a 16 Byte buffer simultaneously in both transmit and receive channels, reducing the number of CPU interrupts while improving system performance.

Ideally suited to industrial applications, the buffered Serial PCI card is compatible with a broad range of operating systems, including Windows, DOS, Linux, and Unix environments.

Backed by a StarTech.com Lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Connect multiple serial devices for a central serial device control system
- Perfect for Manufacturing applications such as CNC machinery, process control equipment, bar code scanners and serial printers
- Designed for use in critical applications with embedded systems and computer based machinery
- Data center applications for serial networking devices, high speed modems, monitoring equipment, long distance communication devices and printers
- Ideal for use in commercial and industrial applications such as POS networks, ATMs, and bank teller stations

Features

- Adds four high speed RS-232 serial ports to your computer
- Works with both 3.3 volt and 5 volt PCI slots
- Breakout cable included
- Transfer rates of up to 921 Kbps
- PCI Bus Version 2.2 compliant

Hardware

Warranty	Lifetime
Ports	4
Interface	Serial
Bus Type	PCI / PCI-X (5 / 3.3V)
Card Type	Standard Profile
Port Style	Dongle (Included)
Industry Standards	RS232
Chipset ID	PLX - PCI9030

Performance

Serial Protocol	RS-232
Max Baud Rate	921.6 Kbps
FIFO	16 Bytes

Connector(s)

Connector Type(s)	PCI / PCI-X (Universal 3.3 & 5V, 32-bit)
External Ports	DB-9 (9 pin, D-Sub)

Software

OS Compatibility	Windows 8 (32bit), 7 (32), Vista(32), XP(32), 2000, NT, 98SE Linux & Unix SCO Open Server
------------------	--

Environmental



Operating Temperature	0C to 55C (32F to 131F)
Storage Temperature	0C to 65C (32F to 149F)
Humidity	5~85% RH

Physical Characteristics

Cable Length	8.3 in [21 cm]
Product Length	5.0 in [12.6 cm]
Product Height	3.9 in [100 mm]

Packaging Information

Package Length	8.6 in [21.8 cm]
Package Width	2.2 in [56 mm]
Package Height	6.0 in [15.3 cm]
Shipping (Package) Weight	16.6 oz [470 g]

What's in the Box

Included in Package	PCI Serial Card
	4 Port DB9 Break-out Cable
	Driver CD
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

