

8 Port PCI RS232 Serial Adapter Card High Speed 16950 cable included

Product ID: PCI8S9503V



The PCI8S9503V 8 Port PCI RS232 Serial Adapter Card High Speed 16950 (cable included) lets you connect up to 8 RS-232 serial devices to the host computer at data rates up to 921 Kbps, and can be installed in either a 3.3V or 5V PCI/PCI-X slot.

The PCI serial card uses a 16 Byte buffer simultaneously in both transmit and receive channels, reducing the number of CPU interrupts while improving system performance.

Ideally suited to industrial applications, the buffered Serial PCI card is compatible with a broad range of operating systems, including Windows, DOS, Linux, and Unix operating environments.

Backed by a StarTech.com Lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Ideal for use in commercial and industrial applications such as POS networks, ATMs, and bank teller stations
- Perfect for Manufacturing applications such as CNC machinery, process control equipment, bar code scanners and serial printers
- Data center applications for serial networking devices, high speed modems, monitoring equipment, long distance communication devices and printers
- Designed for use in critical applications with embedded systems and computer based machinery
- Connect multiple serial devices for a central serial device control system

Features

- Adds eight high speed RS-232 serial ports to your computer
- Transfer rates of up to 921 Kbps
- Breakout cable included
- Works with both 3.3 volt and 5 volt PCI slots
- PCI Bus Version 2.2 compliant

Hardware

Warranty	Lifetime
Ports	8
Interface	Serial
Bus Type	PCI / PCI-X (5 / 3.3V)
Card Type	Standard Profile
Port Style	Dongle (Included)
Chipset ID	PLX - PCI9030

Performance

Serial Protocol	RS-232
Max Baud Rate	921.6 Kbps
FIFO	16 Bytes
Supported Protocols	RS232

Connector(s)

Connector Type(s)	PCI / PCI-X (Universal 3.3 & 5V, 32-bit)
External Ports	DB-9 (9 pin, D-Sub)

Software

OS Compatibility	Windows 8 (32bit), 7 (32), Vista(32), XP(32), 2000, NT, 98SE, 98, 95 Linux (2.2.20 - 3.3) & Unix SCO Open Server
------------------	---

Environmental

Operating Temperature	0C to 55C (32F to 131F)
Storage Temperature	0C to 65C (32F to 149F)
Humidity	5~85% RH

Physical Characteristics

Cable Length	4.0 ft [1.2 m]
Product Length	5.7 in [14.5 cm]
Product Width	0.8 in [20 mm]
Product Height	4.1 in [10.4 cm]
Weight of Product	28.2 oz [800 g]

Packaging Information

Package Length	11.6 in [29.4 cm]
Package Width	2.8 in [70 mm]
Package Height	10.4 in [26.3 cm]
Shipping (Package) Weight	31.1 oz [880 g]

What's in the Box

Included in Package	PCI Serial Card
	8 Port DB9 Break-out Cable
	Driver CD
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

