

## 1U Rackmount Power Switch 8 Outlet 15 Amp RS232 Serial Control PDU

**Product ID:** PCM815SHNA



This 1U Remote Power Switch/Rack PDU is the perfect complement to StarTech.com's IP-based Server Remote Control product line, allowing you to remotely turn power to connected devices on and off.

The PDU can be rackmounted into 1U of cabinet space or used as a standalone power management solution, allowing you to control the power state of devices connected to the power switch/module through an RS232 serial connection.

A cost-effective and efficient rackmount power option, up to 16 1U Remote Power Switches/Rack PDUs can be cascaded together using industry-standard Ethernet patch cables, allowing you to control power to up to 128 devices over a single connection.

Designed for durability and reliability, the 1U Remote Power Switch/Rack PDU is backed by StarTech.com's 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

## Applications

## Features

- Ideal accessory to StarTech.com's Server Remote Control product line, or as a standalone power management solution
- Manage the power requirements of up to 8 computers or other devices from a single switch
- Versatile cascade feature allows you to combine up to 16 power management switches to control up to 128 devices

- Access the features of the power management switch from its easy-to-use software interface or from the front panel
- Easy setup using industry standard cabling and rack-mountable form factor

---

#### Hardware

Warranty	2 Years
Number of Power Outlets	8
Form Factor	Horizontal
Rack-Mountable	Yes

---

#### Performance

Management	RS232
General Specifications	Max Combined Switches: 16 units via UTP Cable Cascade Max. Current load per Port: 6 Amps
Maximum Total Current Draw per Phase	15A

---

#### Connector(s)

Input Connector(s)	IEC 60320 C14 Power
Output Connectors	NEMA 5-15 Power (North America)
Other Interface(s)	9 pin D-Sub (DB-9) Female RJ-45

---

#### Software

OS Compatibility	Optional client software compatible with: Windows 8 (32/64bit), 7 (32/64), Vista(32/64), XP(32/64), 2000 Windows Server 2008 R2, 2008 (32/64), 2003(32/64)
------------------	---

---

#### Special Notes / Requirements

Note	Adding more than 1 optional PCM815SHNA power switch to the Server Remote Control requires a RPORT module
------	--

---

#### Indicators

LED Indicators	Power Alarm State
----------------	----------------------



Current Load Indicator (amps)

Bank Number Indicator

---

**Power**

Input Voltage            120 AC

---

**Environmental**

Operating Temperature    0C to 45C (32F to 113F)

Storage Temperature      -20C to 70C (-4F to 158F)

Humidity                    10~90% RH

---

**Physical Characteristics**

Color                        Black

Product Length            16.1 in [41 cm]

Product Width             6.5 in [16.5 cm]

Product Height            1.8 in [44.5 mm]

---

**Packaging Information**

Package Length            20.6 in [52.2 cm]

Package Width             5.9 in [15.1 cm]

Package Height            14.6 in [37.2 cm]

Shipping (Package) Weight    7.2 lb [3.3 kg]

---

**What's in the Box**

Included in Package        8 Outlet Remote Power Switch

                                      Rackmount Brackets (w/ Screws)

                                      DB9 M/F Cable

                                      RJ45 Cable

                                      Power Cord

                                      Software CD



---

***\*Product appearance and specifications are subject to change without notice.***

