

USB to USB Data Transfer Cable for Windows and Mac

Produkt ID: PCMACLINK2



The PCMACLINK2 USB to USB data transfer cable offers direct file transfers via USB connection between two computers (PC and Mac, PC and PC, Mac and Mac).

The USB data transfer cable eliminates the complicated network setup required to transfer files between computers, or the need to use external storage devices to transfer files back and forth, saving time and hassle.

Once the cable has been connected, a built-in software suite will automatically install on each computer, which not only creates a convenient path for the file transfers but also allows you to sync e-mails from Microsoft Outlook®, synchronize the contents of entire folders, or even share CD/DVD drive access and an Internet connection (between two Windows-based computers).

Certifikat, rapporter och kompatibilitet



Användning

- Migrate important files from an old computer to a new computer.
- Keep files and emails synchronized or create archives between a desktop PC and laptop PC.
- Backup or simply transfer files from a PC to PC, or a PC to Mac, or even Mac to Mac.

- Allow two PCs to share a single available Internet connection and/or CD/DVD-ROM drive.

Funktioner

- Software suite built into the cable itself
- Software enabled functionality includes: Bidirectional file transfer, Microsoft Outlook® email synchronization, File folder synchronization, CD/DVD-ROM sharing, and Internet connection sharing
- Supports USB 2.0 transfer rates of up to 480Mbps
- Built in 5ft cable
- Powered directly from the USB port

Allmänt	UPC	065030840835
	Warranty	2 Years
Särskilda Anmärkningar / Krav	Special Notes	Mac OS only supports the bidirectional file transfer feature. Other features of the software are only available in Windows.
Strömförsörjning	Strömkälla	USB-Powered
Fysiska och Miljörelaterade Egenskaper	Färg	Vit
	Kabinetttyp	Plastic
	Kabellängd	5.0 ft [1.5 m]
	Produktlängd	3.1 in [80 mm]
	Product Width	0.9 in [23 mm]
	Produkthöjd	0.4 in [10 mm]

Produktvikt	1.3 oz [38 g]
Drifttemperatur	0°C to 40°C (32°F to 104°F)
Förvaringstemperatur	-50°C to 70°C (-58°F to 158°F)
Luftfuktighet	0~80%RH

Prestanda

Typ och hastighet	USB 2.0 (480Mbps)
-------------------	-------------------

Hårdvara

Chipset-ID	OTI - 2208
LED-indikatorer	2 - Link/Activity (blue)

Förpackning och Förpackningens Innehåll

Ingår i paketet	1 - USB 2.0 Data Transfer Cable
	1 - Instruction Manual
Paketets bredd	4.2 in [10.6 cm]
Paketets längd	1.0 in [25 mm]
Paketets höjd	6.1 in [15.6 cm]
Fraktvikt (förpackning)	3.2 oz [90 g]

Kontakter

Connector 1 (Quantity)	2
Connector 1	USB-A (480Mbps, 2.5W)

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.