

USB to USB Data Transfer Cable for Windows and Mac

Product ID: PCMACLINK2



The PCMACLINK2 USB to USB data transfer cable offers direct file transfers via USB connection between two computers (PC and Mac, PC and PC, Mac and Mac).

The USB data transfer cable eliminates the complicated network setup required to transfer files between computers, or the need to use external storage devices to transfer files back and forth, saving time and hassle.

Once the cable has been connected, a built-in software suite will automatically install on each computer, which not only creates a convenient path for the file transfers but also allows you to sync e-mails from Microsoft Outlook, synchronize the contents of entire folders, or even share CD/DVD drive access and an Internet connection (between two Windows-based computers).

Certifications, Reports and Compatibility



Applications

- Migrate important files from an old computer to a new computer.
- Keep files and emails synchronized or create archives between a desktop PC and laptop PC.
- Backup or simply transfer files from a PC to PC, or a PC to Mac, or even Mac to Mac.
- Allow two PCs to share a single available Internet connection and/or CD/DVD-ROM drive.

Features

- Software suite built into the cable itself
- Software enabled functionality includes: Bidirectional file transfer, Microsoft Outlook email synchronization, File folder synchronization, CD/DVD-ROM sharing, and Internet connection sharing
- Supports USB 2.0 transfer rates of up to 480Mbps
- Built in 5ft cable
- Powered directly from the USB port

General

UPC	065030840835
Warranty	2 Years

Special Notes / Requirements

Special Notes	Mac OS only supports the bidirectional file transfer feature. Other features of the software are only available in Windows.
---------------	---

Power

Power Source	USB-Powered
--------------	-------------

Physical & Environmental

Color	White
Material	Plastic
Cable Length	5.0 ft [1.5 m]
Product Length	3.1 in [80 mm]
Product Width	0.9 in [23 mm]
Product Height	0.4 in [10 mm]
Weight of Product	1.3 oz [38 g]
Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-50C to 70C (-58F to 158F)
Humidity	0~80%RH

Performance		
	Type and Rate	USB 2.0 (480Mbps)
Hardware		
	Chipset ID	OTI - 2208
	LED Indicators	2 - Link/Activity (blue)
Packaging & In-the-Box		
	Included in Package	1 - USB 2.0 Data Transfer Cable
		1 - Instruction Manual
	Package Width	4.2 in [10.6 cm]
	Package Depth	1.0 in [25 mm]
	Package Height	6.1 in [15.6 cm]
	Shipping (Package) Weight	3.2 oz [90 g]
Connector(s)		
	Connector 1 (Quantity)	2
	Connector 1	USB-A (480Mbps, 2.5W)

****Product appearance and specifications are subject to change without notice.***