

8-Port Rack-Mount PDU with C13 Outlets - 16 A - 10 ft. Power Cord (AS3112) - 1U

Product ID: PDU08C13AU



This rack-mount PDU features eight C13 outlets and you can install it into 1U of rack space to power your rack-mount equipment.

Unlike some rack power solutions that mount awkwardly if at all, this rack-mount PDU is EIA-310D compliant, which ensures a secure and tidy installation into any 19" rack with 1U of available space. Mounting screws and cage nuts are also included to ensure you have everything you need, saving you time and hassle.

For maximum compatibility with your devices, this PDU features C13 outlets which are ideal for a wide range of globally distributed devices including I.T equipment, office equipment, measuring instruments and medical devices. Plus, with a total of eight C13 outlets, the PDU can distribute power to your entire rack.

In the event of random energy surges that can occur during power outages or other anomalies, this PDU prevents costly damages to your equipment with a built-in dual circuit breaker, ensuring your equipment is protected.

The housing of this PDU is also constructed of rugged steel to provide maximum durability in any environment.

The PDU08C13AU is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Note: Although the PDU can provide 16 amps of power to be shared across eight outlets, due to regional limitations, the cord provided is only rated at 15 amps. A user supplied cord and capable outlet would be required to attain the full 16 amp rating.

Certifications, Reports and Compatibility



Applications

- Add eight easily accessible power outlets to your server rack
- Provide power to rack-mounted equipment with C13 power plugs

Features

- Ensure hassle-free installation with a 1U EIA-310D compliant PDU
- Get wide device compatibility with a PDU that features C13 outlets
- 10 ft. (3 m) C19 to AS3112 power cord included
- Protect your equipment with the dual circuit breaker that's built into this PDU
- Solid steel chassis for durability
- 1U rack-mount design

Hardware

Warranty	2 Years
Form Factor	Horizontal
Number of Power Outlets	8
Rack-Mountable	Yes

Performance

General Specifications	Surge Protection: 3600 Joules
	Phase Power: Single phase power adapter
	Included Power Cord: 10 ft [3 m] C19 to AS3112
Maximum Total Current	16A
Maximum Total Current Draw per Phase	16A
Regulatory Derated Input Current (North America)	15A
Nominal Input Voltage	110V - 240V
Nominal Output Voltage	110V - 240V
Maximum Output Voltage	240V

	Load Capacity	3600 VA
Connector(s)		
	Input Connector(s)	1 - IEC C20 (16A, 3 conductor) Power
	Output Connectors	8 - IEC C13 (10A, 3 conductor) Power Receptacle
Special Notes / Requirements		
	Note	Although the PDU can provide 16 amps of power to be shared across eight outlets, due to regional limitations, the cord provided is only rated at 15 amps. A user supplied cord and capable outlet would be required to attain the full 16 amp rating.
Power		
	Input Voltage	100 - 240 AC
Physical Characteristics		
	Material	Steel
	Product Length	3.9 in [10.0 cm]
	Product Width	18.9 in [48.0 cm]
	Product Height	1.7 in [4.4 cm]
	Weight of Product	4.4 lb [2.0 kg]
Packaging Information		
	Package Quantity	1
	Package Length	21.7 in [55.2 cm]
	Package Width	7.5 in [19.0 cm]
	Package Height	3.2 in [8.2 cm]
	Shipping (Package) Weight	4.9 lb [2.2 kg]
What's in the Box		
	Included in Package	1 - rack-mount PDU
		1 - 10 ft [3 m] C19 to AS3112 power cord

4 - M5 screws

4 - M5 cage nuts

1 - instruction manual

**Warranty
Information**

Warranty

2 Years

****Product appearance and specifications are subject to change without notice.***