

Dual Port 40G QSFP+ Network Card - Intel XL710 Open QSFP+ Converged Adapter - PCIe 40 Gigabit Ethernet Server NIC - 40GbE Fiber Optic LAN Card - Dell PowerEdge HPE ProLiant

Product ID: PEX40GQSFPI



Get fast, high-bandwidth connectivity with this QSFP+ server network card. The converged network adapter adds an open QSFP+ slot to your server or workstation. The 40Gb NIC features an Intel controller and provides reliable performance. It's ideal for high-demand database servers, virtualized servers and agile data centers that require infrastructure updates with no downtime.

This QSFP+ server NIC lets you take advantage of the speed and stability of a 40 Gigabit Ethernet network, with data transfers of up to 40Gbps.

With an open QSFP+ slot, the network interface card supports QSFP+ transceiver modules and is compatible with multimode and single-mode fiber, providing a scalable networking solution.

The 40Gb NIC uses an Intel XL710 chipset, providing reliable connectivity and convergent network features. It offers many advanced features including Intel Virtualization Technology for Connectivity.

The PEX40GQSFPI is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Add ultra-fast 40Gbps network connectivity to database, file or application servers and high-performance workstations
- Utilize full 40Gbps network speeds over longer distances than copper cabling
- Ideal for agile and high-demand data centers that require data security, no downtime, and infrastructure updates

Features

- **40GbE QSFP+ NETWORK CARD:** Converged network adapter provides high bandwidth to servers and workstations for demanding applications; includes virtualization (VT-c), SAN and iSCSI offload support
- **TECH SPECS:** 40 Gbps Open QSFP+ Port, MSA Compliant Intel XL710 Chip MMF & SMF Fiber Support PCIe 3.0 x8 PXE Boot 9K Jumbo Frames VT-c VLAN Full & low profile 2 Yr Warr
- **TESTED & VERIFIED PERFORMANCE:** We use Spirent SmartBits validation tools to validate performance; Fiber LAN card compatible w/leading servers like Dell PowerEdge HPE ProLiant & Lenovo ThinkSystem
- **FLEXIBLE:** Use any MSA compliant QSFP+ module / direct attach cable (DAC) supporting different fiber types; 40GbE Network Interface Card works w/leading switch, router, & device brands like Cisco & HPE
- **WIDE HYPEVISOR & OS COMPATIBILITY:** 40 Gigabit Ethernet NIC works w/Windows 7, 8, 8.1, 10; Windows Server 2008 R2, 2012, 2012 R2, 2016, 2019; Linux kernels 3.x + (LTS versions); VMWare ESXi 5.0, 5.1+

Hardware

Warranty	2 Years
Ports	1
Bus Type	PCI Express
Card Type	Standard Profile (LP bracket incl.)
Industry Standards	IEEE 802.3ba 40GBASE-SR4 IEEE 802.3ba 40GBASE-LR4 PCI Express Rev 3.0, using PCIe x8 (or higher) slot
Chipset ID	Intel XL710-BM1

Performance

Maximum Data Transfer Rate	40Gbps
Compatible Networks	40 Gbps
Auto MDIX	Yes
Full Duplex Support	Yes
Jumbo Frame Support	9K max.
Supported Protocols	IEEE 802.3ad (Link Aggregation) IEEE 802.3x (2005 Flow Control Support)

IEEE 802.1Q (VLAN tagging)

Connector(s)

Connector Type(s)	PCI Express x8
Internal Ports	QSFP+

Software

OS Compatibility	Windows 7, 8, 8.1, 10 Windows Server 2008 R2, 2012, 2012 R2, 2016, 2019 (Windows Drivers are supported in 64-bit only) Linux 2.6.24 to 4.11.x (64-bit Only) <i>LTS Versions only</i>
------------------	---

Indicators

LED Indicators	Link LED/Activity LED
----------------	-----------------------

Environmental

Operating Temperature	0C to 57C (32F to 134.6F)
Storage Temperature	-20C to 85C (-4F to 185F)
Humidity	5~95% RH

Physical Characteristics

Color	Black
Material	Steel
Product Length	7.1 in [18.1 cm]
Product Width	4.8 in [12.1 cm]
Product Height	0.8 in [20.0 mm]
Weight of Product	4.0 oz [112.0 g]

Packaging Information

Package Length	8.1 in [20.7 cm]
Package Width	4.5 in [11.4 cm]
Package Height	1.5 in [38.0 mm]



Shipping (Package) Weight	8.5 oz [242.0 g]
------------------------------	------------------

**What's in the
Box**

Included in Package	Network Card
	Low-Profile Bracket
	Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***

