

Nyare version tillgänglig, PEX8S1050LP: StarTech.com 8-ports PCI Express lågprofil seriell kortadapter - seriell adapter- PCIe - RS-232-8 portar

Produkt ID: PEX8S950LP



The PEX8S950LP 8 Port PCI Express Low Profile Serial Adapter Card with dongle cables included offers 8 RS 232 Serial connections via a single PCI Express slot, with data rates up to 921Kbps. Perfect for use with a broad variety of serial peripherals including printers, scanners, industrial controls and more.

A complete 8 port RS232 Serial card solution, the adapter includes 2 breakout cables – each with 4 DB9 connectors for a total of 8 ports. The perfect choice for adding several additional ports when space is at a premium, the serial adapter card is designed to fit in small/micro form factor computer cases. Plus, this versatile card also includes 2 standard profile brackets for compatibility with full size cases.

Backed by a StarTech.com Lifetime warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet



Användning

- Manufacturing (CNC machinery, process control equipment, bar code scanners, serial printers)
- POS (credit/debit card readers, receipt printers, bar code scanners, cash registers, scales)
- Consumer (modems, PDAs, digital cameras, printers)
- Security (UPS control, access key panels, video cameras, card readers, modems)
- Casino (video lottery terminals, slot machines)
- Environmental Control (lighting, temperature, clocks)
- Healthcare (patient monitoring equipment, nurses' stations, modems)
- Hotel Front Desk (serial printers, bar code scanners, keyboard, mouse, receipt printer, credit/debit card reader)
- Hospitality/Restaurant (credit card/debit card reader, serial printers)
- ISDN Networking

Funktioner

- NY MODELL FINNS NU TILLGÄNGLIG: PEX8S1050LP; Lägg till åtta seriella RS-232-portar till datorn via en enda PCI Express-utbyggnadskortplats i lågprofil
- 8 RS232 DB9 connections using a single PCI Express slot
- Breakout cables included
- Provides you with mounting brackets for low profile and standard cases
- Two high performance 16C950 UART channels
- Maximum data transfer rate up to 921kbps
- Compliant with PCI Express specification, revision 1.0a

Hårdvara

Garantipolicy	Lifetime
Portar	8
Gränssnitt	Seriell
Busstyp	PCI Express

	Korttyp	Lågprofil (SP-fästen ingår)
	Porttyp	Dongel (medföljer)
	Chipset-ID	PLX/Oxford - OXmPCI952
Prestanda		
	Seriellt protokoll	RS-232
	Maximal överföringshastighet	921,6 kbps
	Databitar	5, 6, 7, 8, 9
	FIFO	128 Bytes
	Flödeskontroll	RTS/CTS, XON/XOFF
	Paritet	None, Even, Odd, 1, 0
	Stoppbitar	1, 1.5, 2
Kontakt(er)		
	Kontakttyp(er)	1 - PCI Express x1
	Externa portar	8 - DB-9 (9-stifts, D-Sub)
Mjukvara		
	OS-kompatibilitet	Windows® CE 5.0, 98SE, 2000, XP, Vista, 7, 8, 8.1, 10, 11 Windows Server® 2003, 2008 R2, 2012, 2016, 2019 Linux 2.4.x to 4.11.x LTS Versions only
Miljö		
	Drifttemperatur	0°C to 55°C (32°F to 131°F)
	Förvaringstemperatur	-20°C to 85°C (-4°F to 185°F)
	Luftfuktighet	5~95% RH
Utseende		
	Kabellängd	11.0 in [280 mm]
	Produktlängd	6.2 in [15.7 cm]

Produktbredd	0.8 in [2.0 cm]
Produkthöjd	3.1 in [8.0 cm]
Produktvikt	1.2 lb [0.6 kg]

Förpackning

Förpackningsantal	1
Paketets längd	11.2 in [28.5 cm]
Paketets bredd	6.3 in [15.9 cm]
Paketets höjd	2.0 in [5.2 cm]
Fraktvikt (förpackning)	1.6 lb [0.7 kg]

Vad det är i lådan

Ingår i paketet	1 - 8 Port PCI Express Serial Card
	2 - Breakout Cables
	2 - Standard Brackets
	16 - Löstagbara sexkantsskruvar
	1 - Driver CD
	1 - Instruction Manual

Warranty Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.