

Newer version available PEX8S1050LP: StarTech.com 8 Port PCI Express Low Profile Serial Adapter Card - Serial Adapter - PCIe - RS-232-8 Ports

**Product ID:** PEX8S950LP



The PEX8S950LP 8 Port PCI Express Low Profile Serial Adapter Card with dongle cables included offers 8 RS 232 Serial connections via a single PCI Express slot, with data rates up to 921Kbps. Perfect for use with a broad variety of serial peripherals including printers, scanners, industrial controls and more.

A complete 8 port RS232 Serial card solution, the adapter includes 2 breakout cables – each with 4 DB9 connectors for a total of 8 ports. The perfect choice for adding several additional ports when space is at a premium, the serial adapter card is designed to fit in small/micro form factor computer cases. Plus, this versatile card also includes 2 standard profile brackets for compatibility with full size cases.

Backed by a StarTech.com Lifetime warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Manufacturing (CNC machinery, process control equipment, bar code scanners, serial printers)
- POS (credit/debit card readers, receipt printers, bar code scanners, cash registers, scales)
- Consumer (modems, PDAs, digital cameras, printers)
- Security (UPS control, access key panels, video cameras, card readers, modems)
- Casino (video lottery terminals, slot machines)
- Environmental Control (lighting, temperature, clocks)

- Healthcare (patient monitoring equipment, nurses' stations, modems)
- Hotel Front Desk (serial printers, bar code scanners, keyboard, mouse, receipt printer, credit/debit card reader)
- Hospitality/Restaurant (credit card/debit card reader, serial printers)
- ISDN Networking

## Features

- NEW MODEL NOW AVAILABLE: PEX8S1050LP; Add 8 RS-232 serial ports to your computer via a single low profile PCI Express slot
- 8 RS232 DB9 connections using a single PCI Express slot
- Breakout cables included
- Provides you with mounting brackets for low profile and standard cases
- Two high performance 16C950 UART channels
- Maximum data transfer rate up to 921kbps
- Compliant with PCI Express specification, revision 1.0a

---

### Hardware

Warranty	Lifetime
Ports	8
Interface	Serial
Bus Type	PCI Express
Card Type	Low Profile (SP bracket incl.)
Port Style	Dongle (Included)
Chipset ID	PLX/Oxford - OXmPCI952

---

### Performance

Serial Protocol	RS-232
Max Baud Rate	921.6 Kbps
Data Bits	5, 6, 7, 8, 9
FIFO	128 Bytes



Flow Control	RTS/CTS, XON/XOFF
Parity	None, Even, Odd, 1, 0
Stop Bits	1, 1.5, 2

---

#### Connector(s)

Connector Type(s)	PCI Express x1
External Ports	DB-9 (9 pin, D-Sub)

---

#### Software

OS Compatibility	Windows CE 5.0, 98SE, 2000, XP, Vista, 7, 8, 8.1, 10, 11 Windows Server 2003, 2008 R2, 2012, 2016, 2019 Linux 2.4.x to 4.11.x <i>LTS Versions only</i>
------------------	--

---

#### Environmental

Operating Temperature	0C to 55C (32F to 131F)
Storage Temperature	-20C to 85C (-4F to 185F)
Humidity	5~95% RH

---

#### Physical Characteristics

Cable Length	11.0 in [28 cm]
Product Length	6.2 in [15.7 cm]
Product Width	0.8 in [20.0 mm]
Product Height	3.1 in [80.0 mm]
Weight of Product	19.7 oz [559.0 g]

---

#### Packaging Information

Package Length	11.2 in [28.5 cm]
Package Width	6.3 in [15.9 cm]
Package Height	2.0 in [52.0 mm]
Shipping (Package) Weight	25.4 oz [720.0 g]

---

#### What's in the Box



Included in Package	8 Port PCI Express Serial Card
	Breakout Cables
	Standard Brackets
	Removable Hex Nuts
	Driver CD
	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

