

PCIe HDMI Capture Card - 4K 60Hz PCI Express HDMI 2.0 Capture Card w/HDR10 - PCIe x4 Video Capture Device for Desktop - Video Recorder/Adapter/Live Streaming - Supports H.264 - TAA

Product ID: PEXHDCAP4K



You can install the HDMI capture card into any low-profile or full-profile PCIe slot, including fixed workstations such as 2U or 4U rack-mounted servers or media centers.

With frame rates up to 60fps (frames per second) and H.264 encoding, this PCIe HDMI capture card is perfect for capturing ultra high-definition video for editing, compiling, and archiving. HDR10 is available through HDMI 2.0a support.

The software included with the 4K60 capture card encodes captured video in H.264 - the most widely adopted video compression standard in the world. This video recording card ensures your captures are compatible with most device platforms such as PC, Mac, iOS and Android.

The UHD capture card features an HDMI output port so you can watch the video source on a separate HDMI display while recording on your computer.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

PEXHDCAP4K is backed by a StarTech.com 2-year warranty and free, lifetime technical support.

Certifications, Reports and Compatibility





Applications

- Capture meetings, presentations or conference calls directly to your computer
- Upload recorded videos or live broadcast your signal to any online video platform
- Record training and tutorial videos from your laptop or game console

Features

- **4K VIDEO CAPTURE:** PCIe HDMI capture card (minimum x4 slot) captures unprotected 4K 60Hz video to a computer through an HDMI 2.0 input port 4096x2160p 60fps, HDR10, 2ch audio, 16:9 & 4:3 aspect ratio Watch & record in 4K 60Hz simultaneously
- **APPLICATIONS:** Record conference calls, camera feeds, medical imaging in 4K quality with low-latency; Includes Streamcatcher and supports 3rd party (OBS) software; Live streaming on YouTube & other platforms w/RTSP, RTMP; supports Teams & Zoom
- **COMPATIBILITY:** Video capture card/adaptor supports H.264 (MPEG-4) encoding to ensure compatibility with most platforms; Out of the box solution for use with incl. software or third-party options (DirectShow) Includes Low & Full profile brackets
- **OS COMPATIBILITY:** Windows only; PCIe HDMI capture card and Streamcatcher software is compatible with Windows 8-11; Works with NTSC and PAL systems HDCP compliant, will not capture protected-content such as Blu-ray or video output from a Mac
- **THE IT PRO'S CHOICE:** IT professionals choice for over 30 years; This 4K HDMI internal capture card/video grabber is backed for 2-years by StarTech.com, including free 24/5 North America based multi-lingual tech support

Hardware

Warranty	2 Years
AV Input	HDMI - 2.0
AV Output	HDMI
Audio	Yes
Industry Standards	NTSC, PAL-M, PAL-60, PAL
	Video Encoding: MPEG4/H.264
	DirectShow Compatible

Performance

Video Revision	HDMI 2.0
Supported Resolutions	HDMI: 4096 x 2160 (DCI 4K) / 60Hz Additional resolutions and refresh rates may be supported

Connector(s)

Connector A	1 - HDMI (19 pin) 1 - HDMI (19 pin)
Connector B	1 - PCI Express x4

Software

OS Compatibility	Windows 11, 10, 8
------------------	-------------------

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-5C to 40C (23F to 104F)
Humidity	20~80% RH Non-Condensing

Physical Characteristics

Product Length	5.3 in [13.5 cm]
Product Width	4.7 in [12.0 cm]
Product Height	0.7 in [1.7 cm]
Weight of Product	2.0 oz [58.0 g]

Packaging Information

Package Quantity	1
Package Length	8.3 in [21.0 cm]
Package Width	5.6 in [14.3 cm]
Package Height	1.6 in [4.1 cm]
Shipping (Package) Weight	5.2 oz [148.0 g]

What's in the Box

Included in Package	1 - PCI Express HDMI Capture Card
	1 - Low-Profile Bracket
	1 - Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***