

Palo Alto Networks PAN-SFP-PLUS-T Compatible SFP+ Module - 10GBASE-T - SFP+ to RJ45 Cat6/Cat5e - 10GE Gigabit Ethernet SFP+ - RJ-45 30m

Product ID: PLUS-T-ST



The PLUS-T-ST is a Palo Alto Networks PAN-SFP-PLUS-T compatible copper transceiver module that has been designed, programmed and tested to work with Palo Alto Networks brand switches and routers. It delivers dependable 10 GbE connectivity over copper cable, for 100/1000/10GBase-T compliant networks, with a maximum distance of up to 30 m (98.4 ft).

Technical Specifications:

- Maximum Data Transfer Rate: 10 Gbps
- Type: Copper
- Connection Type: RJ-45
- Maximum Transfer Distance: 30 m (98.4 ft)
- MTBF: 510,469,759 hours
- Digital Diagnostics Monitoring (DDM): No

This copper module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility

Applications

Features

- **100% PALO ALTO NETWORKS PAN-SFP-PLUS-T COMPATIBLE SFP+ TRANSCEIVER:** Designed, programmed and tested to work with compatible Palo Alto Networks switches and routers to deliver dependable 10GbE connectivity
- **TECHNICAL SPECS:** 10GBASE-T 10Gbps Copper RJ-45 Connector Distances up to 30m (98.4ft)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Palo Alto Networks routers and switches
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself - not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24.
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

Hardware

Warranty	Lifetime
Compatible Brand	Palo Alto Networks
Industry Standards	IEEE 802.3 100/1000/10000BASE-TX

Performance

Maximum Data Transfer Rate	10.31 Gbps
Max Transfer Distance	30 m (98.4 ft)
Type	Copper
Fiber Operating Mode	Full-Duplex
DDM	No
Compatible Networks	10 Gbps
MTBF	510,469,759 hours

Physical Characteristics

Product Length	0.5 in [13.7 mm]
Product Width	2.7 in [68 mm]



Product Height	0.5 in [13.8 mm]
Weight of Product	0.5 oz [15 g]

Packaging Information

Package Length	4.5 in [11.5 cm]
Package Width	3.5 in [90 mm]
Package Height	1.2 in [31 mm]
Shipping (Package) Weight	1.8 oz [50 g]

What's in the Box

Included in Package	SFP+ Transceiver
---------------------	------------------

****Product appearance and specifications are subject to change without notice.***

