

## 1 Port 10/100 Mbps Parallel Network Print Server

**Product ID:** PM1115P



This 10/100 Mbps Print Server lets you connect a Parallel printer to your Fast Ethernet (10/100Mbps) network, allowing you to share the printer between many networked users, instead of having to purchase separate printers for each individual workstation.

The parallel print server can be installed in minutes and features remote web-based management for simple configuration. The print server features a small footprint design that saves valuable desk space, and can be connected directly into the parallel printer Centronics port and connected to a Fast Ethernet network using standard network cable (RJ45 terminated).

Providing dependable parallel printer sharing, this 10/100Mbps Print Server is backed by StarTech.com's 2-year warranty.

### Certifications, Reports and Compatibility



### Applications

- Connects your Ethernet network to one Parallel printer
- PM1115P offers network printing solution for home, small office, educational & government institutions and any

other environments that require printer sharing

## Features

- Compact and light weight print server only weighs 2.4 ounces
- Compliant with IEEE 1284, IEEE 802.3 & IEEE 802.3u standards
- Configurable using a Web based browser or a Windows based configuration
- Connects directly to the Centronics port of your printer
- Easy setup and configuration
- Eliminates the need to purchase additional printers for individual workstations
- Share 1 printer with computers connected to a home or small office network
- Support SNMP for remote printer management and works with any SNMP based application to access and manage
- Supports 10/100 Mbps fast Ethernet network

---

### Hardware

Warranty	2 Years
Ports	1

---

### Performance

Remote Management Ability	Yes
Supported Protocols	AppleTalk
	IPX/SPX
	NetBEUI
	SNMP
	TCP/IP

---

### Connector(s)

External Ports	1 - Centronics (36 pin)
	1 - RJ-45

---

### Software

OS Compatibility	Windows 8 / 8.1 (32/64bit), 7 (32/64), Vista(32/64), XP(32/64),
------------------	---

2000, ME, 98SE

Windows Server 2012, 2008 R2, 2003(32/64)

Mac OS 10.x (Tested up to 10.10)

Linux

---

#### Special Notes / Requirements

System and Cable Requirements

Ethernet network cable not included

---

#### Indicators

LED Indicators

1 - LAN

1 - Status

1 - Activity

---

#### Power

Power Source

AC Adapter Included

Input Voltage

115V AC

Output Voltage

7.5 DC

Output Current

500mA

Center Tip Polarity

Positive

Plug Type

M

---

#### Physical Characteristics

Color

Beige

Material

Plastic

Product Length

2.2 in [55 mm]

Product Width

2.0 in [5 cm]

Product Height

0.9 in [2.2 cm]

Weight of Product

2.4 oz [67 g]

---

#### Packaging Information

Package Length

9.4 in [24 cm]

Package Width	3.1 in [78 mm]
Package Height	6.2 in [15.8 cm]
Shipping (Package) Weight	1.1 lb [0.5 kg]

---

#### What's in the Box

Included in Package	1 - Parallel Print Server
	1 - Power Adapter (NA)
	1 - Driver CD
	1 - Instruction Manual

---

#### Warranty Information

Warranty	2 Years
----------	---------

---

***\*Product appearance and specifications are subject to change without notice.***