

10/100Mbps Ethernet to USB 2.0 Network LPR Print Server

Product ID: PM1115U2



This palm-sized print server makes it easy to share a USB printer with users on your network. It's the ideal solution for home or small office networks.

Enjoy cost-efficient network printing for multiple users. The USB 10/100 Mbps print server lets you share one USB printer with multiple users on your network, instead of having to buy separate printers for each individual workstation.

With web-based management, you can set up and monitor the printer server through a web browser, so you can place your printer at any convenient shared location - there's no need to put your printer next to your computer. You can send print jobs to another user in your home or office, or even to a printer in another country.

Compact and lightweight, the print server is easy to install with its straightforward installation wizards and remote web-based management. You simply use a USB cable to connect the print server to your printer's USB port, then use an RJ45 networking cable to connect it to the rest of your network.

The printer server supports the Line Printer Remote (LPR) protocol which enables Internet printing. It also supports Bonjour Print Services, making it easier to find and configure printers on your network.

The PM1115U2 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Allows multiple users on an Ethernet network to share one USB printer
- Provides a reliable network printing solution for home, small office, educational and government institutions and any other environments that require printer sharing

Features

- Share a single USB printer with multiple users over a network
- Print from any network computer, across the office
- Provides a reliable Ethernet connection with 10Base-T/100Base-TX auto-sensing
- Compliant with USB 2.0
- Compatible with most standard printers
- Easy to configure using Windows based setup program or web-based management
- Supports LPR network printing, Bonjour Print Services
- Full-duplex support
- Jumbo frame support
- Auto MDI-X support
- Compact housing

Hardware

Warranty	2 Years
Ports	1
Industry Standards	Compliant with IEEE 802.3 10BASE-T and IEEE 802.3u 100BASE-TX
Chipset ID	EST - EST2862B

Performance

Maximum Data Transfer Rate	100 Mbps
Max Distance	100 m / 330 ft
Remote Management Ability	Yes
Auto MDIX	Yes
Full Duplex Support	Yes
Jumbo Frame Support	9K max.
Supported Protocols	LPR



Connector(s)

External Ports	RJ-45
	USB Type-A (4 pin) USB 2.0

Software

OS Compatibility	Windows XP, 7, 8 / RT, 10
	Windows Server 2003, 2008 R2, 2012
	Mac OS 10.6 to 10.10

Special Notes / Requirements

System and Cable Requirements	USB printer cable not included
	Printer with USB connection
Note	OS Compatibility refers to the included software only - the Print Server itself can be used without software on most platforms that support network printing

Indicators

LED Indicators	Power
	Link
	Activity

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.25
Output Voltage	5 DC
Output Current	1A
Center Tip Polarity	Positive
Plug Type	H
Power Consumption (In Watts)	2



Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10% ~ 90% RH

Physical Characteristics

Color	Black
Material	Plastic
Product Length	2.1 in [53 mm]
Product Width	2.1 in [54 mm]
Product Height	0.9 in [23 mm]
Weight of Product	2.2 oz [62 g]

Packaging Information

Package Length	8.5 in [21.5 cm]
Package Width	5.9 in [14.9 cm]
Package Height	2.1 in [54 mm]
Shipping (Package) Weight	11.5 oz [326 g]

What's in the Box

Included in Package	<ul style="list-style-type: none"> USB 2.0 network LPR print server universal power adapter (NA/JP, UK, EU, ANZ) quick start guide RJ45 network cable software CD
---------------------	--

**Product appearance and specifications are subject to change without notice.*

