

1 Port USB Wireless N Network Print Server with 10/100 Mbps Ethernet Port - 802.11b/g/n - TAA

Produkt-ID: PM1115UW



The PM1115UW Wireless-N Print Server lets you share a standard USB printer with multiple users simultaneously over a WiFi network, or a wired LAN connection.

This compact wireless print server supports 802.11b/g/n wireless standards for functionality with almost any wireless network, plus, serving as a primary or backup interface the print server also offers an RJ45 port for 10/100 Mbps wired connections. Providing wireless network printing access enables you to place your printer in any location with network access and avoids the added cost of purchasing individual printers for each workstation or area.

This wireless USB print server can have you up and running in minutes, using either a web-based interface or a Windows® based installation wizard, and also features a WiFi Protected Setup (WPS) button for quick and easy connection to your wireless network. Compatibility with USB 2.0 standards and a wide variety of USB printers and operating systems makes this network print server perfect for installation into mixed environments, with Simple Network Management Protocol (SNMP) support for remote monitoring.

Zertifikate Berichte und Kompatibilität





Anwendungen

- Convert a standard USB printer into a standalone, wireless printer and share between multiple networked computers
- A convenient network printing solution for education and government institutions
- Eliminate the performance issues of an always-on, dedicated PC acting as the printer server

Merkmale

- **SHARE A PRINTER:** This compact wireless print server supports 802.11b/g/n wireless standards for functionality with almost any wireless network and offers an RJ45 port for 10/100 Mbps wired connections
- **DETAILED INSTALLATION STEPS:** Perform initial setup following our online step-by-step instructional video or user manual; Access the online FAQs and IT Pro Community for additional helpful tips and instructions
- **GREAT FOR ANY ENVIRONMENT:** This USB print server adapter is the perfect printing solution; It's ideal for home or small office applications, and places that require shared printing capabilities
- **BROAD COMPATIBILITY:** This USB to Ethernet print server is USB 2.0 compliant, and works w/ Mac & Windows; The print adapter also supports Simple Network Management Protocol; NOTE: iOS, iPadOS, and Airprint are not supported
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this wireless network print server is backed for 2 years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Garantiebestimmungen	2 Years
Ports	1
Schnittstelle	USB 2.0
	RJ45 (10/100-Ethernet)
	Drahtlos
Industrienormen	IEEE 802.3 10BASE-T, IEEE 802.3u 100BASE-T, IEEE 802.11b/g/n Wireless

Leistung

Kompatible Netzwerke	10/100 Mbit/s
Frequenz	2.4 GHz
Sicherheitsmerkmale	WEP-Datenverschlüsselung WPA and WPA2-PSK Data Encryption
Unterstützte Protokolle	TCP/IP (LDP / LPR Printer Port) IPX NetBEUI AppleTalk SNMP SMB over IP

Steckverbinder

Steckverbindertyp(en)	1 - USB 2.0 Typ-A (4 pin, 480Mbit/s) 1 - RJ-45 1 - Wireless N (IEEE 802.11n)
-----------------------	--

Software

Betriebssystemkompatibilität	Windows® XP, Vista, 7, 8, 8.1, 10, 11 Windows Server® 2003, 2008 R2, 2012, 2016, 2019, 2022 Mac OS 10.x, 9.x Linux (Nur LTS Versionen)
------------------------------	---

Spezielle Hinweise/Anforderungen

System- und Kabelanforderungen	USB printer cable not included
Hinweis	The device is compatible with any operating system that supports network printing. Please note that the included software is compatible with Windows only.

Anzeiger	LED-Anzeiger	1 - Status
		1 - USB
		1 - WLAN
Strom	Stromversorgung	Mit Netzadapter
	Eingangsspannung	100 - 240 AC
	Eingangsstrom	0.3 A
	Ausgangsspannung	5 DC
	Ausgangsstrom	1 A
	Polarität der Mittelspitze	Positiv
	Steckertyp	N
	Stromverbrauch	5
Umgebungsbedingungen	Betriebstemperatur	0°C to 50°C (32°F to 122°F)
	Lagertemperatur	-5°C to 65°C (23°F to 149°F)
	Feuchtigkeit	0~70% RH (Non-Condensing)
Physische Eigenschaften	Farbe	Weiß
	Gehäusotyp	Kunststoff
	Produktlänge	2.8 in [72 mm]
	Produktbreite	2.3 in [5.8 cm]
	Produkthöhe	1.0 in [2.5 cm]
	Produktgewicht	1.8 oz [52 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	6.1 in [15.4 cm]
Paketbreite	9.0 in [22.9 cm]
Pakethöhe	2.7 in [6.8 cm]
Versandgewicht (Verpackung)	9.0 oz [254.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - Wireless Print Server
	1 - Power Adapter
	1 - Software CD
	1 - Quick Install Guide

Garantieinformationen

Warranty	2 Jahre
----------	---------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.