

## 1 Port USB Wireless N Network Print Server with 10/100 Mbps Ethernet Port - 802.11 b/g/n

**Product ID:** PM1115UW



The PM1115UW Wireless-N Print Server lets you share a standard USB printer with multiple users simultaneously over a WiFi network, or a wired LAN connection.

This compact wireless print server supports 802.11b/g/n wireless standards for functionality with almost any wireless network, plus, serving as a primary or backup interface the print server also offers an RJ45 port for 10/100 Mbps wired connections. Providing wireless network printing access enables you to place your printer in any location with network access and avoids the added cost of purchasing individual printers for each workstation or area.

This wireless USB print server can have you up and running in minutes, using either a web-based interface or a Windows based installation wizard, and also features a WiFi Protected Setup (WPS) button for quick and easy connection to your wireless network. Compatibility with USB 2.0 standards and a wide variety of USB printers and operating systems makes this network print server perfect for installation into mixed environments, with Simple Network Management Protocol (SNMP) support for remote monitoring.

### Certifications, Reports and Compatibility



## Applications

- Convert a standard USB printer into a standalone, wireless printer and share between multiple networked computers
- A convenient network printing solution for education and government institutions
- Eliminate the performance issues of an always-on, dedicated PC acting as the printer server

## Features

- **SHARE A PRINTER:** This compact wireless print server supports 802.11b/g/n wireless standards for functionality with almost any wireless network and offers an RJ45 port for 10/100 Mbps wired connections
- **DETAILED INSTALLATION STEPS:** Perform initial setup following our online step-by-step instructional video or user manual; Access the online FAQs and IT Pro Community for additional helpful tips and instructions
- **GREAT FOR ANY ENVIRONMENT:** This USB print server adapter is the perfect printing solution; It's ideal for home or small office applications, and places that require shared printing capabilities
- **BROAD COMPATIBILITY:** This USB to Ethernet print server is USB 2.0 compliant, and works w/ Mac & Windows; The print adapter also supports Simple Network Management Protocol; NOTE: iOS, iPadOS, and Airprint are not supported
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this wireless network print server is backed for 2 years, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	2 Years
Ports	1
Interface	USB 2.0
	RJ45 (10/100 Ethernet)
	Wireless Ethernet
Industry Standards	IEEE 802.3 10BASE-T, IEEE 802.3u 100BASE-T, IEEE 802.11b/g/n Wireless

---

### Performance

Compatible Networks	10/100 Mbps
Frequency	2.4 GHz
Security Features	WEP Data Encryption

Supported Protocols		WPA and WPA2-PSK Data Encryption
		TCP/IP (LDP / LPR Printer Port)
		IPX
		NetBEUI
		AppleTalk
		SNMP
		SMB over IP
<hr/>		
Connector(s)		
	Connector Type(s)	1 - USB 2.0 Type-A (4 pin, 480Mbps)
		1 - RJ-45
		1 - Wireless N (IEEE 802.11n)
<hr/>		
Software		
	OS Compatibility	Windows XP, Vista, 7, 8, 8.1, 10, 11
		Windows Server 2003, 2008 R2, 2012, 2016, 2019, 2022
		Mac OS 10.x, 9.x
		Linux (<i>LTS Versions only</i>)
<hr/>		
Special Notes / Requirements		
	System and Cable Requirements	USB printer cable not included
	Note	The device is compatible with any operating system that supports network printing. Please note that the included software is compatible with Windows only.
<hr/>		
Indicators		
	LED Indicators	1 - Status
		1 - USB
		1 - WLAN
<hr/>		
Power		
	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC

Input Current	0.3 A
Output Voltage	5 DC
Output Current	1 A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption (In Watts)	5

---

#### Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-5C to 65C (23F to 149F)
Humidity	0~70% RH (Non-Condensing)

---

#### Physical Characteristics

Color	White
Material	Plastic
Product Length	2.8 in [72 mm]
Product Width	2.3 in [5.8 cm]
Product Height	1.0 in [2.5 cm]
Weight of Product	1.8 oz [52 g]

---

#### Packaging Information

Package Quantity	1
Package Length	9.1 in [23.0 cm]
Package Width	6.2 in [15.8 cm]
Package Height	2.5 in [6.4 cm]
Shipping (Package) Weight	9.9 oz [280.0 g]

---

#### What's in the Box

Included in Package	1 - Wireless Print Server
	1 - Power Adapter
	1 - Software CD
	1 - Quick Install Guide

---

***\*Product appearance and specifications are subject to change without notice.***