

## Industrial Gigabit Ethernet PoE Injector - 30W 802.3at PoE+ Midspan 48V-56VDC DIN Rail Power Over Ethernet Injector Adapter - -40C to +75C Cameras/Sensors/WiFi Access

**Product ID:** POEINJ30W



This Gigabit Power over Ethernet (PoE+) injector supplies power and data connectivity to a Gigabit PoE-compliant device using a standard Ethernet cable.

Provides up to 30W of power (midspan) to IEEE 802.3af (PoE / Type 1) and IEEE 802.3at (PoE+ / Type 2) powered devices (PD) like:

- Cameras
- Sensors
- Wi-fi access points

Uses Cat 5e (or higher rated) Ethernet cabling.

Industrial features include -40 C to 75 C operating temperature, IP-30 rated housing, vibration, shock, and free-fall standard testing.

- Vibration: EN 60068-2-6
- Shock: EN 60068-2-27
- Free-fall: EN 60068-2-32

600,000+ hours MTBF rating using Telcordia/Bellcore at 50C for long-term reliability.

Dual power inputs provide redundancy. Accepts terminal block power or coaxial power connectors with the barrel plug adapter, allowing the product to be hardwired or powered using an external power supply (not included), which does not require professional installation.

The POEINJ30W is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

## Applications

## Features

- **30 WATT GIGABIT ETHERNET PoE INJECTOR:** Provides up to 30W of power (midspan) to IEEE 802.3af (PoE / Type 1) and IEEE 802.3at (PoE+ / Type 2) PD devices like cameras, sensors, and wi-fi access points
- **TECH SPECS:** 1 Gbps 48V-56VDC input IEEE 802.3af / IEEE 802.3at (30W) 10/100/1000 Mbps auto negotiation Link fault passthrough (LFP) 16K Jumbo frames IP-30 housing DIN rail/wall mountable
- **DUAL POWER INPUTS:** Includes a barrel plug adapter for terminal block power, allowing the product to be hardwired or power powered using a standard AC/DC wall adapter
- **ROBUST DESIGN:** Industrial Power over Ethernet Injector w/MTBF of 600,000+ hrs @ 50C Vibration, shock & free fall rated Rugged IP-30 aluminum housing Hardened operating temp of -40C to 75C
- **STARTECH.COM ADVANTAGE:** IT professionals' choice for over 30 years This PoE Injector is backed for 2-years by StarTech.com, including free 24/5 North America based multi-lingual tech support

---

### Hardware

Warranty	2 Years
PoE	Yes
Industry Standards	IEEE 802.3 10BASE-T, IEEE 802.3u 100BASE-TX, IEEE 802.3ab 1000BASE-T, IEEE 802.3af Power over Ethernet, IEEE 802.3at PoE+
Chipset ID	Microsemi PD69101

---

### Performance

Maximum Cable Length	328.0 ft [100 m]
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Jumbo Frame Support	9K max.
General Specifications	ESD: IEC 61000-4-2: Contact: 6KV; Air: 8KV, EFT: IEC 61000-4-4: Power: 2KV; Signal: 2KV, Surge: IEC 61000-4-5: Power: 2KV; Signal: 2KV, Vibration: EN 60068-2-6, Shock: EN 60068-2-27, Free-fall: EN 60068-2-32, Housing: IP-30, Safety: MET (UL) 60950-1, Safety: EN60950-1, Reverse polarity

protection, Overload current protection

MTBF 630,899 hours

Supported Protocols CSMA/CD, IEEE 802.3

IEEE 802.3at PoE+

IEEE 802.3af PoE

---

**Connector(s)**

Connector A Ethernet 10/100  
RJ-45 (PoE+)

---

**Special Notes / Requirements**

Patents and Licenses United States Patent No. 5,406,260 (expired) , United States Patent No. 6,650,622, United States Patent No. 7,457,250, United States Patent No. 8,155,012, United States Patent No. 8,902,760, United States Patent No. 8,942,107, United States Patent No. 9,019,838, United States Patent No. 9,049,019, United States Patent Application No. 14/695,456, United States Patent Application No. 14/726,940,

---

**Indicators**

LED Indicators PW1, PW2  
Mode A

---

**Power**

Plug Type N  
Power Consumption (In Watts) Max 37W

---

**Environmental**

Operating Temperature -40C to 75C  
Storage Temperature -40C to 85C  
Humidity 5 to 95% (non-condensing)

---

**Physical Characteristics**

Color Black  
Material Aluminum



Product Length	0.0 in [0.0 mm]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	5.0 oz [143.0 g]

---

**Packaging Information**

Package Length	6.4 in [16.2 cm]
Package Width	8.3 in [21.1 cm]
Package Height	2.5 in [64.0 mm]
Shipping (Package) Weight	13.0 oz [367.0 g]

---

**What's in the Box**

Included in Package	PoE Injector
	Terminal Block
	Terminal Block to Barrel Power Connector Adapter
	Mounting Hardware Kit
	Quick-Start Guide

---

***\*Product appearance and specifications are subject to change without notice.***

