

19in 12U Sliding Rotating Open Frame Network Rack - 4 Post AV/Data Rack - 16.7" Deep Slide-Out IT Equipment Rack w/Cable Management Pull Out/Pivoting Computer/Communications Rack

Product ID: PORACK12U



This 12U slide-out server rack helps you save space while keeping your rack-mount equipment organized and accessible. The compact open-frame rack is easy to pull out and rotate, which makes it easy to install and access your equipment or perform maintenance when needed.

The rack supports a total load capacity of 125 lb. (56.7 kg).

Save space in your office or server room

The rack helps you save valuable floor space. It's designed for installation in small areas such as below a table or in a cabinet or cupboard. Its versatility makes this the perfect rack for storing your servers in a boardroom, small office/home office, restaurant or any place where space is at a premium.

Keep your equipment cool and accessible

For easy equipment installation and maintenance, the 12U server rack's base is on sliding rails, which means it's easier to access the back of your equipment. With its open-frame design, the rack not only maximizes accessibility but also offers unobstructed airflow to your equipment, providing passive cooling to keep your rack-mounted equipment running at optimal temperatures.

Save money on shipping

The rack comes in a flat-packed box, which reduces shipping volume and significantly lowers cost when compared to racks that ship fully assembled. Plus, because the rack is packaged efficiently, it's easy to transport and store.

The PORACK12U is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Rack-mounting A/V equipment in a radio or television studio

Features

- **UNIQUE SLIDE OUT & ROTATE DESIGN:** 19" 4 post open frame network rack ideal for installation in built-in cabinet & easily slides out up to 18.7in. rotating up to 90 degrees for easy access to equipment
- **INTEGRATED CABLE MANAGEMENT:** Keeps cables organized in this AV/Data/IT/Communications rack, and helps make pull-out access easy and tangle-free; cables can be routed down and under the rack if needed
- **TECH SPECS:** Max. Mounting Depth 16.7 in. Max. Extension Depth 40.5 in. EIA/ECA-310-E Compliant 125lb (56.7kg) Capacity Cage Nuts & Screws incl.
- **EASY SHIPPING & ASSEMBLY:** Pivoting Computer Equipment rack comes in a convenient flat-pack shipping form factor with an easy to assemble design that includes cage nuts & screws to mount your equipment
- **THE STARTECH.COM ADVANTAGE:** StarTech.com offers a 2-year warranty and free lifetime technical support on this 12U rack and has been the choice of IT professionals and businesses for over 30 years

Hardware

Warranty	2 Years
Wallmountable	No
Rack Type	4-Post
Frame Type	Open Frame
U Height	12U
Special Features	Built-in Cable Management
	Easy Assembly
	U-Markings
Mounting Rail Profile	L-Shape

	Mounting Hole Types	Square (For Cage Nut)
	Industry Standards	EIA/ECA-310-E
Performance		
	Weight Capacity	125.0 lb [56.7 kg]
Physical Characteristics		
	Color	Black
	Construction Material	Steel
Product Measurements		
	Product Length	22.4 in [56.8 cm]
	Product Width	19.2 in [48.7 cm]
	Product Height	24.2 in [61.5 cm]
	Weight of Product	51.5 lb [23.4 kg]
	Maximum Mounting Depth	16.7 in [42.5 cm]
Packaging Information		
	Flat Pack (Assembly Required)	Yes
	Package Length	24.8 in [63.0 cm]
	Package Width	21.5 in [54.5 cm]
	Package Height	8.7 in [22.0 cm]
	Shipping (Package) Weight	58.4 lb [26.5 kg]
What's in the Box		
	Included in Package	1 - Sliding Tray
		1 - Top Bracket
		6 - Vertical Rails
		1 - Stabilizing Plate
		1 - Security Plate

4 - Narrow Cable Managers

1 - Cable Manager

2 - Thumbscrews

24 - Assembly Screws

24 - Assembly Nuts

48 - M5 Cage Nuts

48 - M5 Screws

1 - User Manual

****Product appearance and specifications are subject to change without notice.***