

2 Port 12V 24V PoweredUSB Adapter Card - USB PlusPower

Produkt ID: PUSBADAP



The PUSBADAP 2 port 12V/24V Powered USB Adapter Card acts as the daughter board component to StarTech.com's 3 Port PCI 12V Powered USB Card (PCI312PUSB), adding two Powered USB (USB PlusPower) ports and expanding the number of Powered USB ports provided, for a total of five.

Alternatively, the adapter card can be used as a standalone 2 port Powered USB card without taking up a PCI slot by simply connecting the provided USB header cable to the motherboard, and a standard LP4 power connection from the system power supply.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet



Användning

- Ideal for adding portable scanners, receipt printers, and digital scales to new Retail Point-of-Sale (POS), or Point-of-Care (POC) PCs
- Install into integrated Kiosks to provide power to Parking Garage/Gas Station receipt printers
- Provide power and data connection to remote surveillance cameras
- Upgrade Mobile Computing systems such as delivery services/overland transportation vehicles

- Gaming industry (joysticks with feedback mechanisms)
- External CD-ROM, DVD drive and Hard drives that require more than 500mA current

Funktioner

- Doesn't occupy a PCI slot
- Provides 2 powered USB ports that supply 24V and 12V power
- Connect as a daughter board to a PoweredUSB card, or to the motherboard of a PC using the included USB header cable
- 4 pin Din connector acts as an optional external 24V AC adapter
- Provides 3A of current per port
- Backwards compatible with USB 2.0 and 1.1
- Maximum data transfer rate of 480 Mbps

Hårdvara

Garantipolicy	Lifetime
Portar	2
Korttyp	Standardprofil

Kontakt(er)

Interna portar	1 - IDC (10-stifts, moderkortskontakt)
	1 - LP4 (4-stift, Molex-type Large Drive Power)
Externa portar	1 - Power DIN (4-stifts)
	1 - PoweredUSB 12V (8-stifts, värdsida)
	1 - PoweredUSB 24V (8-stifts, värdsida)

Mjukvara

OS-kompatibilitet	Windows® 2000/ME/2003/XP/Vista
-------------------	--------------------------------

Särskilda anmärkningar/krav

Obs. Operates in two separate modes: Connect from the internal USB connector to the main board on the Powered USB card

Stand Alone Mode connects via internal USB connect to the Mother Board of the PC

Utseende

Produktlängd	4.7 in [12 cm]
Produktbredd	2.6 in [6.7 cm]
Produktvikt	7.1 oz [200 g]

Förpackning

Paketets längd	8.9 in [22.7 cm]
Paketets bredd	1.7 in [43 mm]
Paketets höjd	6.4 in [16.3 cm]
Fraktvikt (förpackning)	0.4 lb [0.2 kg]

Vad det är i lådan

Ingår i paketet	1 - Daughter Board
	1 - USB Header Cable
	1 - Instruction Manual

Warranty Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.