

2ft (60cm) Power Extension Cord, C14 to C13, 10A 125V, 18AWG, Computer Power Cord Extension, IEC-320-C14 to IEC-320-C13 AC Power Cable Extension for Power Supply, UL Listed

**Product ID:** PXT1002



The PXT1002 2-foot Computer Power Cord Extension Cable can be used to connect your PDU or monitor to your PC, or as an extension cable for your existing computer power cord.

Expertly designed and constructed of high quality materials, the power extension cable ( C14 to C13) features one computer power (female) connector and one hooded (male) power connector.

This high quality Power Cord Extension Cable is backed by our Lifetime Warranty.

## Certifications, Reports and Compatibility



## Applications

- Extend your monitor, scanner, printer, or PC power cord by an additional 2 ft
- Replace worn-out or missing power cords with this high quality power cord extension

## Features

- **AC POWER CORD:** This 2ft (60cm) 18AWG power supply extension cable with IEC 60320 C14 and IEC 60320 C13 connectors is suitable for workstation/home office use. Rated to carry 125V at 10A.

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief connectors for durability Fire Rating: VW-1 3 Conductor extension cord made with 100% copper wire This C14 to C13 power extension cord is available in other lengths
- **SPECS:** 2ft (0.6m) AC Power Cord IEC 60320 C14 to IEC 60320 C13 18AWG 125V 10A (Max) Jacket Type: SVT Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.24in (6.1mm)
- **COMPATIBILITY:** PC Power Cord IEC 60320 C14 works with North American outlets IEC C13 connector works with most desktop computers, servers, PDUs, UPS, printers, and more Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

#### Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SVT

#### Connector(s)

Connector A	1 - IEC 60320 C14 Power
Connector B	1 - IEC 60320 C13 Power

#### Special Notes / Requirements

Note	UL Listed
------	-----------

#### Power

Input Voltage	125V AC
Input Current	10 A

#### Physical Characteristics

Color	Black
Wire Gauge	18 AWG
Cable Length	2.0 ft [0.6 m]
Product Length	24.0 in [61.0 cm]
Product Width	1.1 in [2.9 cm]
Product Height	0.8 in [2.1 cm]

Weight of Product	2.8 oz [78.0 g]
-------------------	-----------------

---

#### Packaging Information

Package Quantity	1
Package Length	8.1 in [20.5 cm]
Package Width	7.7 in [19.5 cm]
Package Height	1.1 in [2.7 cm]
Shipping (Package) Weight	3.1 oz [88.0 g]

---

#### What's in the Box

Included in Package	1 - 2 ft Standard Computer Power Cord Extension - C14 to C13
---------------------	--

---

#### Warranty Information

Warranty	Lifetime
----------	----------

---

***\*Product appearance and specifications are subject to change without notice.***