

10ft (3m) Power Extension Cord Splitter, C14 to 2x C13, 13A 250V, 16AWG, Computer Power Cord Extension, IEC 320 C14 to 2x C13 AC Power Cable Extension for Power Supply, UL Listed

Product ID: PXT100Y



The PXT100Y 10ft Computer Power Cord features one C14 and two C13 power connections, allowing two devices to share one power port connection - freeing up space on your power strip, surge protector, or wall outlet.

Great for computers, monitors, or printers, this Y Power Cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Plug two computers, monitors and/or printers into a single power port on a power strip, surge protector or wall outlet

Features

- **AC POWER CORD SPLITTER:** This 10ft (3m) 16AWG power supply extension cable with IEC 60320 C14 and 2x IEC 60320 C13 connectors is suitable for workstation/home office use. Rated to carry 250V at 13A.
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817). Fully molded strain relief connectors for durability. Fire Rating: VW-1. 3 Conductor extension cord made with 100% copper wire. This C14 power extension cord splitter is available in other lengths.
- **SPECS:** 3m (10ft) AC Power Cord. IEC 60320 C14 to 2x IEC 60320 C13. 16AWG. 250V 13A (Max). Jacket Type:

SJT Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.24in (6.1mm)

• COMPATIBILITY: PC Power Cord IEC 60320 C14 works with North American cables IEC C13 connector works with most desktop computers, servers, PDUs, UPS, printers, and more Replacement PC power supply cable/cord

• THE IT PRO'S CHOICE: Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	1 - IEC 60320 C14 Power
Connector B	2 - IEC 60320 C13 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	250V AC
Input Current	13A

Physical Characteristics

Color	Black
Wire Gauge	16 AWG
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Product Width	2.0 in [5.1 cm]
Product Height	0.6 in [1.6 cm]
Weight of Product	12.5 oz [354.0 g]

Packaging Information

Package Quantity	1
Package Length	10.2 in [26.0 cm]
Package Width	9.7 in [24.7 cm]
Package Height	2.2 in [5.5 cm]
Shipping (Package) Weight	1.1 lb [0.5 kg]

What's in the Box

Included in Package	1 - 10 ft Computer Power Cord Splitter IEC320 C14 to 2x IEC320 C13
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***