

10ft (3m) Computer Power Cord, NEMA 5-15P to C13, 10A 125V, 10 Pack, 18AWG, Black Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable - UL Listed

Produkt-ID: PXT1011010PK



This 10 pack of 10ft long computer power cords provides suitable replacement cords for your worn-out or missing PC and monitor power cables.

Designed with dependability in mind, these universal monitor power cords are built with 18 AWG wire and are rated to carry 125V at 10A.

Constructed with fully molded strain relief connectors, the 10-pack computer or screen power cables ensure a reliable and durable connection for your devices.

Featuring a NEMA 5-15p 3 prong plug and a C13 connector, these replacement desktop power cords are compatible with most monitors, PCs, scanners and laser printers.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to our customers. Our local StarTech.com Technical Advisors have a broad product expertise and work directly with StarTech.com Engineers to provide support for our customers both pre and post-sales.

PXT1011010PK is backed by a StarTech.com lifetime warranty and free lifetime technical support.

## Zertifikate Berichte und Kompatibilität



## Anwendungen

- Plugs monitor, PC, laser printer, or scanner into a grounded power outlet

## Merkmale

- **AC POWER CORD:** This 10ft (3m) 18AWG flexible computer power cable 10 Pack with NEMA 5-15P and IEC 60320 C13 connectors is suitable for workstation/home office use | Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief connectors for durability | 3 Conductor Power Cable made from 100% Copper Wire | Fire Rating: VW-1
- Ausgelegt für 125 V bei 10 A
- **COMPATIBILITY:** NEMA 5-15P works with North American electrical outlets | IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more | Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance | This C13 power cord is available in other lengths

---

### Hardware

Garantiebestimmungen	Lifetime
----------------------	----------

Kabeltyp	SVT
----------	-----

---

### Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
------------------	-----------------------------------

Steckverbinder B	1 - IEC 60320 C13 Strom
------------------	-------------------------

---

### Spezielle Hinweise/Anforderungen

Hinweis	UL Listed
---------	-----------

---

### Strom

Eingangsspannung	125 AC
------------------	--------

Eingangsstrom	10A
---------------	-----

---

Physische  
Eigenschaften

Farbe	Schwarz
Drahtstärke	18 AWG
Kabellänge	10.0 ft [3.0 m]
Produktlänge	10.0 ft [3.0 m]
Produktbreite	0.1 in [0.2 cm]
Produkthöhe	0.9 in [2.4 cm]
Produktgewicht	7.9 oz [225.0 g]

Verpackungsinform  
ationen

Paketmenge	10
Paketlänge	11.7 in [29.6 cm]
Paketbreite	8.9 in [22.5 cm]
Pakethöhe	3.7 in [9.5 cm]
Versandgewicht (Verpackung)	4.9 lb [2.2 kg]

Verpackungsinhalt

Im Paket enthalten	10 - Computer-Netzkabel - NEMA5-15P auf C13
--------------------	---

Garantieinformatio  
nen

Warranty	Lifetime
----------	----------

\* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.