

## 6 ft Standard Computer Power Cord - NEMA5-15P to C13 - 10 Pack

Produkt-ID: PXT10110PK



The 10 pack 6 ft universal computer power cord lets you plug a monitor, PC, or laser printer into a grounded power outlet.

Note: The length is measured from mold to mold, excluding the prongs on the male end

Backed by StarTech.com's lifetime warranty, this high quality NEMA5-15P to C13 computer power cable is constructed to provide a durable, reliable connection.

## Zertifikate Berichte und Kompatibilität



## Anwendungen

### Merkmale

- **VERSATILE FUNCTIONALITY:** The 10 pack 6 ft (length measured from mold to mold, excluding the prongs on the male end) computer power cord lets you plug a monitor, PC, or laser printer into a grounded power outlet
- **STURDY DESIGN:** This high quality, 18 AWG computer power cable is constructed to provide a durable, reliable connection

- **MEETS INDUSTRY STANDARDS:** The NEMA5-15P to C13 universal replacement power cord is a UL listed component, hence meeting all necessary industry level safety requirements
- **HIGH QUALITY REPLACEMENT:** Replace worn-out or missing power cords with this high quality, 6ft standard computer power cord
- **THE STARTECH.COM ADVANTAGE:** StarTech.com offers a lifetime warranty and free lifetime technical support on this 6ft power cord and has been the choice of IT professionals and businesses for over 30 years

---

#### Hardware

|                       |          |
|-----------------------|----------|
| Garantiebestimmungen  | Lifetime |
| Anzahl von Leitern    | 3        |
| Steckverbinderplatten | Nickel   |
| Kabeltyp              | SVT      |

---

#### Steckverbinder

|                  |                                   |
|------------------|-----------------------------------|
| Steckverbinder A | 1 - NEMA 5-15 Strom (Nordamerika) |
| Steckverbinder B | 1 - IEC 60320 C13 Strom           |

---

#### Strom

|                  |        |
|------------------|--------|
| Eingangsspannung | 125 AC |
| Eingangsstrom    | 10A    |

---

#### Umgebungsbedingungen

|                    |              |
|--------------------|--------------|
| Betriebstemperatur | -20 to 60 °C |
| Lagertemperatur    | -20 to 60 °C |
| Feuchtigkeit       | 0 to 70%     |

---

#### Physische Eigenschaften

|              |                |
|--------------|----------------|
| Farbe        | Schwarz        |
| Drahtstärke  | 18 AWG         |
| Produktlänge | 6.0 ft [1.8 m] |

|                |                 |
|----------------|-----------------|
| Produktbreite  | 1.0 in [2.5 cm] |
| Produkthöhe    | 0.9 in [2.4 cm] |
| Produktgewicht | 3.3 lb [1.5 kg] |

---

#### Verpackungsinformationen

|                             |                   |
|-----------------------------|-------------------|
| Paketmenge                  | 1                 |
| Paketlänge                  | 13.8 in [35.0 cm] |
| Paketbreite                 | 18.1 in [46.0 cm] |
| Pakethöhe                   | 4.3 in [11.0 cm]  |
| Versandgewicht (Verpackung) | 3.4 lb [1.5 kg]   |

---

#### Verpackungsinhalt

|                    |                                                           |
|--------------------|-----------------------------------------------------------|
| Im Paket enthalten | 10 - 6 ft Standard Computer Power Cord - NEMA5-15P to C13 |
|--------------------|-----------------------------------------------------------|

---

#### Garantieinformationen

|          |          |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

---

\* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.