

10ft (3m) Heavy Duty Power Cord, NEMA 5-15P to C13 AC Power Cord, 15A 125V, 14AWG, Replacement Computer Power Cord, Monitor Power Cable, NEMA 5-15P to IEC 60320 C13 Power Cord - PC Power Supply Cable

Produkt-ID: PXT1011410



The PXT1011410 Computer Power Cord features 14 AWG wire capable of high power connections, making it a reliable solution for connecting large servers to PDUs (Power Distribution Units).

This durable, universal power cord can be used as a cost-effective replacement for your existing PC power cord, or for plugging a monitor, PC, or laser printer into a grounded power outlet.

Backed by StarTech.com's lifetime warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Connect large servers to PDUs
- Make a power connection up to 10ft between your PC and monitor

Merkmale

- **HEAVY DUTY AC POWER CORD:** This 10ft (3m) 14AWG universal power cord with NEMA 5-15P and IEC 60320 C13 connectors is suitable for workstation/home office use | Rated to carry 125V at 15A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief connectors for durability | Fire Rating: VW-1 | 3 Conductor Power Cable made with 100% Copper Wire | This C13 thick gauge computer power cord is available in other lengths
- **SPECS:** 10ft (3m) AC Power Cord | NEMA 5-15P to IEC 60320 C13 | 14AWG | 125V 15A(Max) | Jacket Type: SJT | Jacket Material: PVC | Black | Temperature Range: 37°F to 140°F (3°C to 60°C) | Cable Outer Diameter: 0.3in (7.6mm)
- **COMPATIBILITY:** PC Power Cord NEMA 5-15P works with North American outlets | IEC C13 connector works with most desktop computers, servers, monitors, PDUs, printers, and more | Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 3-prong power cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Typ der Kabelummantelung	PVC - Polyvinyl Chloride

Leistung

Max. Kabellänge	10.0 ft [3.0 m]
-----------------	-----------------

Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
Steckverbinder B	1 - IEC 60320 C13 Strom

Spezielle Hinweise/Anforderungen

Hinweis	UL Listed
---------	-----------

Strom

Eingangsspannung	125 AC
Eingangsstrom	15A

Umgebungsbedingungen

Betriebstemperatur	-20°C to 60°C (-4°F to 140°F)
Lagertemperatur	-20°C to 60°C (-4°F to 140°F)

Physische Eigenschaften

Farbe	Schwarz
Drahtstärke	14 AWG
Kabellänge	10.0 ft [3.0 m]
Produktlänge	10.0 ft [3.0 m]
Produktbreite	1.0 in [2.4 cm]
Produkthöhe	0.9 in [2.4 cm]
Produktgewicht	1.0 lb [0.5 kg]

Verpackungsinformationen

Paketmenge	1
Paketlänge	12.2 in [30.9 cm]
Paketbreite	3.4 in [8.6 cm]
Pakethöhe	2.2 in [5.5 cm]
Versandgewicht (Verpackung)	15.8 oz [448.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 10ft 14 AWG Computer Power Cord - NEMA5-15P to C13
--------------------	--

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.