

3ft (1m) Heavy Duty Power Cord, NEMA 5-15P to C13 AC Power Cord, 15A 125V, 14AWG, Replacement Computer Power Cord, Monitor Power Cable, NEMA 5-15P to IEC 60320 C13 Power Cord - PC Power Supply Cable

**Product ID:** PXT101143



The PXT101143 NEMA 5-15P to C13 Computer Power Cord (3ft) features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher rated, heavier gauge cable, and connecting to Power Distribution Units (PDU).

This high-quality power cord can be used as a cost-effective replacement for your existing PC power cord, or for plugging a monitor, PC, or laser printer into a grounded power outlet.

Backed by Lifetime warranty, the PXT101143 is designed and constructed for maximum durability and reliability.

## Certifications, Reports and Compatibility



## Applications

- Connecting large servers to a PDU
- Connect your monitor, PC, or laser printer into a grounded power outlet

## Features

- **HEAVY DUTY AC POWER CORD:** This 3ft (1m) 14AWG universal power cord with NEMA 5-15P and IEC 60320

C13 connectors is suitable for workstation/home office use Rated to carry 125V at 15A

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief connectors for durability Fire Rating: VW-1 3 Conductor Power Cable made with 100% Copper Wire This C13 thick gauge computer power cord is available in other lengths

- **SPECS:** 3ft (1m) AC Power Cord NEMA 5-15P to IEC 60320 C13 14AWG 125V 15A (Max) Jacket Type: SJT Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.3in (7.6mm)

- **COMPATIBILITY:** PC Power Cord NEMA 5-15P works with North American outlets IEC C13 connector works with most desktop computers, servers, monitors, PDUs, printers, and more Replacement PC power supply cable/cord

- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 3-prong power cable is backed for life, including free lifetime 24/5 multilingual technical assistance

---

#### Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

---

#### Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - IEC 60320 C13 Power

---

#### Special Notes / Requirements

Note	UL Listed
------	-----------

---

#### Power

Input Voltage	125 AC
Input Current	15 A

---

#### Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	3.0 ft [0.9 m]
Product Length	36.0 in [91.4 cm]

Weight of Product 5.9 oz [167 g]

---

**Packaging Information**

Package Quantity 1

Package Length 10.0 in [25.5 cm]

Package Width 4.9 in [12.5 cm]

Package Height 1.0 in [25 mm]

Shipping (Package) Weight 6.1 oz [172 g]

---

**What's in the Box**

Included in Package 1 - 3 ft 14 AWG Computer Power Cord – NEMA 5-15P to C13

---

*\*Product appearance and specifications are subject to change without notice.*