

1ft (30cm) Computer Power Cord, NEMA 5-15P to C13, 10A 125V, 18AWG, Black Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable - UL Listed

Produkt-ID: PXT1011



This 1ft IBM Power Cord lets you plug a monitor, PC, or laser printer into a grounded power outlet.

Backed by StarTech.com's lifetime warranty, this high quality IBM power cable is constructed to provide a durable, reliable connection.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **AC POWER CORD:** This 1ft (30cm) 18AWG flexible computer power cable with NEMA 5-15P and IEC 60320 C13 connectors is suitable for workstation/home office use | Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief connectors for durability | 3 Conductor Power Cable made from 100% Copper Wire | Fire Rating: VW-1
- **SPECS:** 1ft (30cm) Power Cable | NEMA 5-15P to IEC 60320 C13 | 18AWG | 125V 10A (Max) |

Jacket Rating: SVT | Jacket Material: PVC | Color: Black | Temperature Range: 37°F to 140°F (3 to 60) | Cable Outer Diameter: 0.25in (6.3mm)

- **COMPATIBILITY:** NEMA 5-15P works with North American electrical outlets | IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more | Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance | This C13 power cord is available in other lengths

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Kabeltyp	SVT

Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
Steckverbinder B	1 - IEC 60320 C13 Strom

Spezielle Hinweise/Anforderungen

Hinweis	UL Listed
---------	-----------

Strom

Eingangsspannung	125 AC
Eingangsstrom	10A

Physische Eigenschaften

Farbe	Schwarz
Drahtstärke	18 AWG
Kabellänge	1.0 ft [0.3 m]
Produktlänge	12.0 in [30.5 cm]

Produktbreite	0.9 in [2.3 cm]
Produkthöhe	2.3 in [5.9 cm]
Produktgewicht	2.0 oz [58.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	5.6 in [14.1 cm]
Paketbreite	7.9 in [20.0 cm]
Pakethöhe	1.1 in [2.8 cm]
Versandgewicht (Verpackung)	2.3 oz [66.0 g]

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.