

25ft (7.6m) Computer Power Cord, NEMA 5-15P to C13, 10A 125V, 18AWG, Black
Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor
Power Cable - UL Listed

Produkt-ID: PXT10125



The PXT10125 25-foot Computer Power Cord is a durable, universal power cord that can be used as a cost effective replacement for your existing PC power cord, and offers 25ft of connection distance between a computer or peripheral device and an available power outlet - an ideal solution for connecting your monitor, PC or laser printer to a grounded power outlet.

Backed by StarTech.com's lifetime warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Plugs monitor, PC, or laser printer into a grounded power outlet

Merkmale

- AC POWER CORD: This 25ft (7.6m) 18AWG flexible computer power cable with NEMA 5-15P and IEC 60320 C13 connectors is suitable for workstation/home office use | Rated to carry 125V at 10A

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief connectors for durability | 3 Conductor Power Cable made from 100% Copper Wire | Fire Rating: VW-1
- **SPECS:** 25ft (7.6m) Power Cable | NEMA 5-15P to IEC 60320 C13 | 18AWG | 125V 10A (Max) | Jacket Rating: SVT | Jacket Material: PVC | Color: Black | Temperature Range: 37°F to 140°F (3 to 60) | Cable Outer Diameter: 0.25in (6.3mm)
- **COMPATIBILITY:** NEMA 5-15P works with North American electrical outlets | IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more | Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance | This C13 power cord is available in other lengths

Hardware

Garantiebestimmungen Lifetime

Anzahl von Leitern 3

Steckverbinder

Steckverbinder A 1 - NEMA 5-15 Strom (Nordamerika)

Steckverbinder B 1 - IEC 60320 C13 Strom

Spezielle Hinweise/Anforderungen

Hinweis UL Listed

Strom

Eingangsspannung 125 AC

Eingangsstrom 10A

Physische Eigenschaften

Farbe Schwarz

Drahtstärke 18 AWG

Kabellänge 25.0 ft [7.6 m]

Produktlänge 25.0 ft [7.6 m]

Produktbreite 1.0 in [2.4 cm]

Produkthöhe 0.9 in [2.4 cm]

Produktgewicht 1.0 lb [0.5 kg]

Verpackungsinformationen

Paketmenge	1
Paketlänge	6.7 in [17.0 cm]
Paketbreite	7.8 in [19.9 cm]
Pakethöhe	1.9 in [4.7 cm]
Versandgewicht (Verpackung)	1.2 lb [0.5 kg]

Verpackungsinhalt

Im Paket enthalten	1 - 25ft Standard Computer Power Cord - NEMA5-15P to C13
--------------------	--

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.