

3ft (1m) Computer Power Cord, NEMA 5-15P to C13, 10A 125V, 18AWG, Black
Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor
Power Cable - UL Listed

Produkt-ID: PXT101_3



Our 3ft IBM Power Cable will let you plug a monitor, PC, or laser printer into a grounded power outlet.

This 3ft. power cable is expertly designed and constructed of only top quality materials, and is backed by our Lifetime Warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **AC POWER CORD:** This 3ft (1m) 18AWG flexible computer power cable with NEMA 5-15P and IEC 60320 C13 connectors is suitable for workstation/home office use | Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief connectors for durability | 3 Conductor Power Cable made from 100% Copper Wire | Fire Rating: VW-1
- **SPECS:** 3ft (1m) Power Cable | NEMA 5-15P to IEC 60320 C13 | 18AWG | 125V 10A (Max) | Jacket

Rating: SVT | Jacket Material: PVC | Color: Black | Temperature Range: 37°F to 140°F (3 to 60) | Cable Outer Diameter: 0.25in (6.3mm)

- **COMPATIBILITY:** NEMA 5-15P works with North American electrical outlets | IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more | Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance | This C13 power cord is available in other lengths

Hardware

Garantiebestimmungen Lifetime

Anzahl von Leitern 3

Kabeltyp SVT

Steckverbinder

Steckverbinder A 1 - NEMA 5-15 Strom (Nordamerika)

Steckverbinder B 1 - IEC 60320 C13 Strom

Spezielle Hinweise/Anforderungen

Hinweis UL Listed

Strom

Eingangsspannung 125V (max.)

Eingangsstrom 10A

Physische Eigenschaften

Farbe Schwarz

Drahtstärke 18 AWG

Kabellänge 3.0 ft [0.9 m]

Produktlänge 36.0 in [91.4 cm]

Produktbreite 1.0 in [2.5 cm]

Produkthöhe 0.9 in [2.4 cm]

Produktgewicht	3.5 oz [98.0 g]
----------------	-----------------

Verpackungsinformationen

Paketmenge	1
Paketlänge	2.6 in [6.5 cm]
Paketbreite	7.8 in [19.9 cm]
Pakethöhe	1.4 in [3.5 cm]
Versandgewicht (Verpackung)	3.5 oz [100.0 g]

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.