

6 ft Standard Computer Power Cord - NEMA5-15P to C13

Product ID: PXT101



The 6 ft universal computer power cord lets you plug a monitor, PC, or laser printer into a grounded power outlet.

Note: The length is measured from mold to mold, excluding the prongs on the male end

Backed by StarTech.com's lifetime warranty, this high quality NEMA5-15P to C13 computer power cable is constructed to provide a durable, reliable connection.

Certifications, Reports and Compatibility

Applications

- Plugs monitor, PC, or laser printer into a grounded power outlet

Features

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Type	SVT

Connector(s)

Connector A	NEMA 5-15 Power (North America)
-------------	---------------------------------

Connector B IEC 60320 C13 Power

Special Notes / Requirements

Note UL Listed

Power

Input Voltage 125 AC

Input Current 10A

Environmental

Operating Temperature -20 to 60 C

Storage Temperature -20 to 60 C

Humidity 0 to 70%

Physical Characteristics

Color Black

Wire Gauge 18 AWG

Cable Length 6.0 ft [1.8 m]

Product Length 6.0 ft [1.8 m]

Product Width 1.0 in [24.9 mm]

Product Height 0.9 in [24.0 mm]

Weight of Product 5.0 oz [141.0 g]

Packaging Information

Package Length 8.7 in [22.0 cm]

Package Width 7.9 in [20.0 cm]

Package Height 1.5 in [38.0 mm]

Shipping (Package) Weight 5.3 oz [150.0 g]

What's in the Box

Included in Package 6 Ft. IBM Power Cable



****Product appearance and specifications are subject to change without notice.***

