

3ft (1m) Computer Power Cord, NEMA 5-15P to Right Angle C13, 10A 125V, 18AWG, Black Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable - UL Listed

Produkt-ID: PXT101L3



This NEMA 5-15P to C13 power cord connects to your hard-to-reach peripheral devices.

The right-angled C13 connector positions the cable so that it's flush with your device, which is perfect for connecting in tight spaces because it doesn't require as much clearance at the connection point as a straight connector. It's perfect for wall-mounted monitors or any device that sits snugly against a wall or is stored in a compact space.

The short 3-foot cable length means less clutter, to ensure a tidy and professional installation.

The PXT101L3 is built to exact specifications and is fully tested to ensure maximum performance. Plus, the cable is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Connect your hard-to-reach computer, monitor, printer or other device to a power outlet

Merkmale

- **AC POWER CORD:** This 3ft (0.9m) 18AWG flexible computer power cable with NEMA 5-15P and Right-Angle IEC 60320 C13 connectors is suitable for workstation/home office use | Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief connectors for durability | 3 Conductor Power Cable made from 100% Copper Wire | Fire Rating: VW-1
- **SPECS:** 3ft (0.9m) Power Cable | NEMA 5-15P to Right-Angle IEC 60320 C13 | 18AWG | 125V 10A (Max) | Jacket Rating: SVT | Jacket Material: PVC | Color: Black | Temperature Range: 37°F to 140°F (3 to 60) | Cable Outer Diameter: 0.25in (6.3mm)
- **COMPATIBILITY:** NEMA 5-15P works with North American electrical outlets | IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more | Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance | This C13 power cord is available in other lengths

Hardware

Garantiebestimmungen Lifetime

Anzahl von Leitern 3

Kabeltyp SVT

Steckverbinder

Steckverbinder A 1 - NEMA 5-15 Strom (Nordamerika)

Steckverbinder B 1 - IEC 60320 C13 Strom

Spezielle Hinweise/Anforderungen

Hinweis UL Listed

Strom

Eingangsspannung 125 AC

Eingangsstrom 10 A

Physische Eigenschaften

Farbe Schwarz

Steckverbinderart	Gerade auf rechtsgewinkelt
Drahtstärke	18 AWG
Kabellänge	3.0 ft [0.9 m]
Produktlänge	36.0 in [91.4 cm]
Produktbreite	1.0 in [2.5 cm]
Produkthöhe	1.8 in [4.5 cm]
Produktgewicht	3.5 oz [98.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	7.9 in [20.1 cm]
Paketbreite	2.6 in [6.6 cm]
Pakethöhe	1.4 in [3.5 cm]
Versandgewicht (Verpackung)	3.7 oz [106.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 3ft Computer Power Cord - NEMA 5-15P to Right-Angle C13
--------------------	---

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.