

3ft (1m) Computer Power Cord, NEMA 5-15P to Right Angle C13, 10A 125V, 18AWG, Black
Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable -
UL Listed

Product ID: PXT101L3



This NEMA 5-15P to C13 power cord connects to your hard-to-reach peripheral devices.

The right-angled C13 connector positions the cable so that it's flush with your device, which is perfect for connecting in tight spaces because it doesn't require as much clearance at the connection point as a straight connector. It's perfect for wall-mounted monitors or any device that sits snugly against a wall or is stored in a compact space.

The short 3-foot cable length means less clutter, to ensure a tidy and professional installation.

The PXT101L3 is built to exact specifications and is fully tested to ensure maximum performance. Plus, the cable is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Connect your hard-to-reach computer, monitor, printer or other device to a power outlet

Features

- AC POWER CORD: This 3ft (0.9m) 18AWG flexible computer power cable with NEMA 5-15P and Right-Angle IEC

60320 C13 connectors is suitable for workstation/home office use Rated to carry 125V at 10A

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief connectors for durability 3 Conductor Power Cable made from 100% Copper Wire Fire Rating: VW-1
- **SPECS:** 3ft (0.9m) Power Cable NEMA 5-15P to Right-Angle IEC 60320 C13 18AWG 125V 10A (Max) Jacket Rating: SVT Jacket Material: PVC Color: Black Temperature Range: 37F to 140F (3 to 60) Cable Outer Diameter: 0.25in (6.3mm)
- **COMPATIBILITY:** NEMA 5-15P works with North American electrical outlets IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance This C13 power cord is available in other lengths

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Type	SVT

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - IEC 60320 C13 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	10 A

Physical Characteristics

Color	Black
Connector Style	Straight to Right Angle
Wire Gauge	18 AWG
Cable Length	3.0 ft [0.9 m]
Product Length	36.0 in [91.4 cm]

Product Width	1.0 in [2.5 cm]
Product Height	1.8 in [4.5 cm]
Weight of Product	3.5 oz [98.0 g]

Packaging Information

Package Quantity	1
Package Length	7.9 in [20.1 cm]
Package Width	2.6 in [6.6 cm]
Package Height	1.4 in [3.5 cm]
Shipping (Package) Weight	3.7 oz [106.0 g]

What's in the Box

Included in Package	1 - 3ft Computer Power Cord - NEMA 5-15P to Right-Angle C13
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***