

6ft (1.8m) Computer Power Cord, NEMA 5-15P to Right Angle C13, 10A 125V, 18AWG, Black Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable - UL Listed

Produkt-ID: PXT101L



This 6ft Right Angle Power Cord features a standard NEMA 5-15P connector as well as a right-angled C13 connector allowing you to plug a monitor, PC, or laser printer into a grounded power outlet.

The right angle C13 connector positions the shaft of the cable flush with the back of the device you are connecting, saving space at the connection point. Backed by Lifetime Warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Plugs monitor, PC, or laser printer into a grounded power outlet
- CSA approved

Merkmale

- AC POWER CORD: This 6ft (1.8m) 18AWG flexible computer power cable with NEMA 5-15P and Right-Angle IEC 60320 C13 connectors is suitable for workstation/home office use | Rated to carry

125V at 10A

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief connectors for durability | 3 Conductor Power Cable made from 100% Copper Wire | Fire Rating: VW-1
- **SPECS:** 6ft (1.8m) Power Cable | NEMA 5-15P to Right-Angle IEC 60320 C13 | 18AWG | 125V 10A (Max) | Jacket Rating: SVT | Jacket Material: PVC | Color: Black | Temperature Range: 37°F to 140°F (3 to 60) | Cable Outer Diameter: 0.25in (6.3mm)
- **COMPATIBILITY:** NEMA 5-15P works with North American electrical outlets | IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more | Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance | This C13 power cord is available in other lengths

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Kabeltyp	SVT

Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
Steckverbinder B	1 - IEC 60320 C13 Strom

Spezielle Hinweise/Anforderungen

Hinweis	UL Listed
---------	-----------

Strom

Eingangsspannung	125 AC
Eingangsstrom	10A

Physische Eigenschaften

Farbe	Schwarz
Drahtstärke	18 AWG
Kabellänge	6.0 ft [1.8 m]

Produktlänge	6.0 ft [1.8 m]
Produktbreite	1.7 in [4.4 cm]
Produkthöhe	1.0 in [2.5 cm]
Produktgewicht	5.4 oz [152.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	7.9 in [20.1 cm]
Paketbreite	3.1 in [8.0 cm]
Pakethöhe	1.4 in [3.5 cm]
Versandgewicht (Verpackung)	5.9 oz [166.0 g]

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.