

10ft (3m) Laptop Power Cord, NEMA 5-15P to C5 (Clover Leaf), 10A 125V, 18AWG, Laptop Replacement Cord, Printer Power Cable, Laptop Charger Cord, Laptop Power Brick Cord - UL Listed

Produkt-ID: PXT101NB3S10



The PXT101NB3S10 10-foot 3-Slot Laptop Power Cord features one NEMA 5-15P and one C5 connector - a suitable replacement notebook power cord or spare power cord for your HP, Toshiba or other compatible laptop.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Spare/replacement cable for your laptop
- Laptop accessory for mobile professionals

Merkmale

- AC POWER CORD: This 10ft (3m) 18AWG flexible laptop power cord with NEMA 5-15P and IEC 60320 C5 connectors is suitable for workstation/home office use | Rated to carry 125V at 10A
- PERFORMANCE AND SAFETY: UL listed (UL62 & UL817) | Fully molded strain relief C5 connector for

durability | Fire Rating: VW-1 | 3 Conductor Notebook Power Cable made with 100% Copper Wire

- SPECS: 10ft (3m) Power Cable | NEMA 5-15P to IEC 60320 C5 | 18AWG | 125V 10A (Max) | Jacket Rating: SVT | Jacket Material: PVC | Color: Black | Temperature Range: 35°F to 140°F (2 to 60) | Cable Outer Diameter: 0.3in (7.62mm)

- COMPATIBILITY: AC Power Cord NEMA 5-15P works with North American outlets | IEC C5 connector works with most power bricks for laptops/notebooks, monitors, scanners, printers, and more | Replacement laptop power supply cable/cord

- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this laptop charger cord is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Garantiebestimmungen	Lifetime
----------------------	----------

Anzahl von Leitern	3
--------------------	---

Kabeltyp	SVT
----------	-----

Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
------------------	-----------------------------------

Steckverbinder B	1 - IEC 60320 C5 Strom
------------------	------------------------

Spezielle Hinweise/Anforderungen

Hinweis	UL Listed
---------	-----------

Strom

Eingangsspannung	125 AC
------------------	--------

Eingangsstrom	10A
---------------	-----

Physische Eigenschaften

Farbe	Schwarz
-------	---------

Drahtstärke	18 AWG
-------------	--------

Kabellänge	10.0 ft [3.0 m]
------------	-----------------

Produktlänge	10.0 ft [3.0 m]
--------------	-----------------

Produktbreite	1.0 in [2.5 cm]
---------------	-----------------

Produkthöhe	0.8 in [2.0 cm]
Produktgewicht	10.4 oz [295.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	7.0 in [17.8 cm]
Paketbreite	7.8 in [19.9 cm]
Pakethöhe	1.7 in [4.2 cm]
Versandgewicht (Verpackung)	11.1 oz [314.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 10 ft Standard Laptop Power Cord - NEMA 5-15P to C5
--------------------	---

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.