

10ft (3m) Computer Power Cord, NEMA 5-15P to 2x IEC 320 C13, 10A 125V, 18AWG, Black Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable - UL Listed

Produkt-ID: PXT101Y10



This C13 Y-cable lets you plug multiple devices into a single power outlet, to maximize the space on your power strip, surge protector or wall outlet. It's perfect for setting up dual monitor arms.

The cable length from the Y-split is 30 inches on each side. This gives you an extended reach for connecting to two monitors securely, without placing a strain on the cable.

You can also use the power-splitter cable to connect a monitor and computer, or any two devices that have a C13 power connection, to the same outlet.

The PXT101Y10 is built to exact specifications and is fully tested to ensure maximum performance. Plus, the cable is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Power two devices from a single power outlet

Merkmale

- **AC POWER Y CABLE:** This 10ft (3m) 18AWG flexible computer power Y cable with NEMA 5-15P and 2x IEC 60320 C13 connectors is suitable for workstation/home office use | Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief connectors for durability | 3 Conductor Power Y cable made from 100% copper wire | Fire Rating: VW-1
- **SPECS:** 10ft (3m) Power Y cable | NEMA 5-15P to 2x IEC 60320 C13 | 18AWG | 125V 10A (Max) | Jacket Rating: SVT | Jacket Material: PVC | Color: Black | Temperature Range: 37°F to 140°F (3 to 60) | Y cable Outer Diameter: 0.25in (6.3mm)
- **COMPATIBILITY:** NEMA 5-15P works with North American electrical outlets | IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more | Replacement PC power supply Y cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance | This C13 power cord is available in other lengths

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Kabeltyp	SVT

Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
Steckverbinder B	2 - IEC 60320 C13 Strom

Spezielle Hinweise/Anforderungen

System- und Kabelanforderungen	The cable length from the Y split is 30 inches on each side.
--------------------------------	--

Strom

Eingangsspannung	125 AC
Eingangsstrom	10 A

Physische
Eigenschaften

Farbe	Schwarz
Drahtstärke	18 AWG
Kabellänge	10.0 ft [3.0 m]
Produktlänge	10.0 ft [3.0 m]
Produktgewicht	13.1 oz [372 g]

Verpackungsinform
ationen

Paketmenge	1
Paketlänge	8.2 in [20.9 cm]
Paketbreite	3.3 in [8.3 cm]
Pakethöhe	2.0 in [5.2 cm]
Versandgewicht (Verpackung)	13.1 oz [372.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 10ft NEMA 5-15P to 2x C13
--------------------	-------------------------------

Garantieinformatio
nen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.