

6ft (2m) Computer Power Cord Y Splitter, NEMA 5-15P to 2x C13, 10A 125V, 18AWG, Black AC Power Splitter Cord, PC Power Supply Cable, Dual Monitor Power Cable - UL Listed

Produkt-ID: PXT101Y



Our 6 ft IBM Power Cord lets you plug a monitor, PC, or laser printer into a grounded power outlet.

Backed by StarTech.com's lifetime warranty, this high quality IBM power cable is constructed to provide a durable, reliable connection.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Connects two monitors, PC's, or laser printers into a grounded power outlet
- Ideal when you're running out of space on your power/surge protector or wall outlets

Merkmale

- AC POWER CORD: This 6ft (2m) 18AWG flexible computer power cable with NEMA 5-15P and 2x IEC 60320 C13 connectors is suitable for workstation/home office use | Rated to carry 125V at 10A

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief connectors for durability | 3 Conductor Power Cable made from 100% Copper Wire | Fire Rating: VW-1
- **SPECS:** 6ft (2m) Power Cable | NEMA 5-15P to 2x IEC 60320 C13 | 18AWG | 125V 10A (Max) | Jacket Rating: SJT | Jacket Material: PVC | Color: Black | Temperature Range: 37°F to 140°F (3 to 60) | Cable Outer Diameter: 0.3in (7.8mm)
- **COMPATIBILITY:** NEMA 5-15P works with North American electrical outlets | IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more | Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance | This C13 power cord is available in other lengths

Hardware

Garantiebestimmungen Lifetime

Kabeltyp SVT

Steckverbinder

Steckverbinder A 1 - NEMA 5-15 Strom (Nordamerika)

Steckverbinder B 2 - IEC 60320 C13 Strom

Spezielle Hinweise/Anforderungen

Hinweis UL Listed

Strom

Eingangsspannung 125 AC

Eingangsstrom 10A

Physische Eigenschaften

Farbe Schwarz

Drahtstärke 18 AWG

Kabellänge 6.0 ft [1.8 m]

Produktlänge 6.0 ft [1.8 m]

Produktgewicht 9.3 oz [263 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	9.1 in [23.1 cm]
Paketbreite	3.2 in [8.2 cm]
Pakethöhe	2.3 in [5.8 cm]
Versandgewicht (Verpackung)	9.7 oz [274.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 6 ft Standard Y Computer Power Cord NEMA 5-15P to 2x C13
--------------------	--

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.