

6ft (2m) UK Computer Power Cable Y Splitter, 18AWG, BS 1363 to 2x C13, 10A 250V, Black
Replacement AC Power Cord, Kettle Lead / Dual UK Power Cord, PC Power Supply Cable,
TV/Monitor Power Cable

Product ID: PXT101YUK



This C13 Y-cable lets you plug multiple devices into a single power outlet, to maximize the space on your power strip, surge protector or wall outlet. It's perfect for setting up dual-monitor workstations.

The cable length from the Y-split is 47 cm on each side. This gives you an extended reach for connecting to two monitors securely, without placing a strain on the cable.

The power-splitter cable can also be used for connecting a monitor and computer to the same outlet or any two devices that have a C13 power connection.

The PXT101YUK is built to exact specifications and is fully tested to ensure maximum performance. Plus, the cable is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Power two devices from a single power outlet

Features

- **AC POWER CORD:** This 6ft (1.8m) 18AWG UK computer power cable with BS 1363 and 2x IEC C13 connectors is suitable for workstation/home office use. Rated to carry 250V at 10A.
- **PERFORMANCE AND SAFETY:** Fully molded ends for durability and VDE approved connectors. 3 Conductor Power Cable made from 100% Copper Wire. Fire Rating: VW-1. CE Certified.
- **SPECS:** 6ft (1.8m) Power Cord. BS 1363 to 2x IEC 60320 C13. 18AWG (0.75mm²). 250V 10A (Max). Jacket Rating: H05VV-F. Jacket Material: PVC. Color: Black. Temperature Range: 10 to 60. Cable Outer Diameter: 6.8mm.
- **COMPATIBILITY:** BS 1363 works with UK electrical outlets. IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more. Replacement PC power supply cable/cord, Kettle Lead.
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cable is backed for life, including free lifetime 24/5 multi-lingual technical assistance. This C13 power cord is available in other lengths.

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SVT

Connector(s)

Connector A	1 - BS 1363 Power (UK)
Connector B	2 - IEC 60320 C13 Power

Special Notes / Requirements

Note	The cable length from the Y split is 47 cm on each side.
------	--

Power

Input Voltage	250 AC
Input Current	10 A

Physical Characteristics

Color	Black
Wire Gauge	0.75mm ²
Cable Length	6.0 ft [1.8 m]
Product Length	5.9 ft [1.8 m]

Product Width	2.2 in [5.5 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	11.6 oz [330.0 g]

Packaging Information

Package Quantity	1
Package Length	11.8 in [30.0 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.8 in [4.5 cm]
Shipping (Package) Weight	11.8 oz [334.0 g]

What's in the Box

Included in Package	1 - 6ft BS1363 to 2x C13 cable
---------------------	--------------------------------

****Product appearance and specifications are subject to change without notice.***