

10ft (3m) Heavy Duty Power Cord, NEMA 5-15P to C19 AC Power Cord, 15A 125V, 14AWG, Computer Power Cord, Heavy Gauge Power Cable for PDUs and Network Equipment, NEMA 5-15P to IEC 60320 C19 Power Cord

Product ID: PXT515191410



This NEMA 5-15P-to-C19 power cord features 14 AWG wire that's suitable for high-power connections, making it perfect for high-end server equipment such as routers, switches, Power Distribution Units (PDU), etc.

Plus, you can use the cable to extend the reach of your existing power cord by 10 feet, which gives you the extra distance you need to place your devices according to your server room configuration.

Expertly designed and constructed of high-quality materials, the StarTech.com PXT515191410 power cord is backed by a lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Connect your high-power server equipment to a power outlet
- Extend your existing power cord by 10 feet

Features

- **HEAVY DUTY AC POWER CORD:** This 10ft (3m) 14AWG universal power cord with NEMA 5-15P and IEC 60320

C19 connectors is suitable for workstations/home office use Rated to carry 125V at 15A

• **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief connectors for durability Fire Rating: VW-1 3 Conductor Power Cable made with 100% Copper Wire This C19 thick gauge computer power cord is available in other lengths

• **SPECS:** 10ft (3m) AC Power Cord NEMA 5-15P to IEC 60320 C19 14AWG 125V 15A (Max) Jacket Type: SJT Jacket Material: PVC Black Temperature Range: 37F to 167F (3C to 75C) Cable Outer Diameter: 0.36in (9.1mm)

• **COMPATIBILITY:** PC Power Cord NEMA 5-15P works with North American outlets IEC C19 connector works with most servers and networking equipment Replacement PC power supply cable/cord

• **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 3-prong power cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - IEC 60320 C19 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	15 A

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]

Weight of Product	17.3 oz [490 g]
-------------------	-----------------

Packaging Information

Package Quantity	1
Package Length	9.7 in [24.6 cm]
Package Width	3.9 in [10.0 cm]
Package Height	2.8 in [7.2 cm]
Shipping (Package) Weight	1.1 lb [0.5 kg]

What's in the Box

Included in Package	1 - 10 ft 14 AWG Computer Power Cord - NEMA 5-15P to IEC 320 C19
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***