

8ft (2.4m) Heavy Duty Power Cord, NEMA 5-15P to C15 AC Power Cord, 15A 125V, 14AWG, Replacement Computer Power Cord, Monitor Power Cable, NEMA 5-15P to IEC 60320 C15 Power Cord - PC Power Supply Cable

Produkt-ID: PXT515C158



The PXT515C158 8-foot Computer Power Cord features a C15 connector rated for high-temperature equipment, as well as 14 AWG wire suitable for high power connections - a reliable solution for connecting to NEMA 5-15P Power Distribution Units (PDU) located in switchgear rooms and data center environments, or large server applications that require a higher rated, heavier gauge cable.

Designed and constructed of high quality materials, this 5-15P to C15 power cable is backed by our Lifetime Warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Compatible with Cisco, HP and other hardware devices with C15 power connections
- Connect large servers to PDUs, even in high-temperature environments

Merkmale

- **HEAVY DUTY AC POWER CORD:** This 8ft (2.4m) 14AWG universal power cord with NEMA 5-15P and IEC 60320 C15 connectors is suitable for workstations/home office use | Rated to carry 125V at 15A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief connectors for durability | Fire Rating: VW-1 | 3 Conductor Power Cable made with 100% Copper Wire | This C15 thick gauge computer power cord is available in other lengths
- **SPECS:** 8ft (2.4m) AC Power Cord | NEMA 5-15P to IEC 60320 C15 | 14AWG | 125V 15A (Max) | Jacket Type: SJT | Jacket Material: PVC | Black | Temperature Range: 37°F to 221°F (3°C to 105°C) | Cable Outer Diameter: 0.36in (9.1mm)
- **COMPATIBILITY:** PC Power Cord NEMA 5-15P works with North American outlets | IEC C15 connector works with most servers and networking equipment | Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 3-prong power cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Kabeltyp	SJT

Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
Steckverbinder B	1 - IEC 60320 C15 Strom

Spezielle Hinweise/Anforderungen

Hinweis	UL Listed
---------	-----------

Strom

Eingangsspannung	125 AC
Eingangsstrom	15 A

Physische Eigenschaften

Farbe	Schwarz
-------	---------

Drahtstärke	14 AWG
Kabellänge	8.0 ft [2.4 m]
Produktlänge	8.0 ft [2.4 m]
Produktgewicht	14.0 oz [396 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	8.7 in [22.2 cm]
Paketbreite	5.3 in [13.5 cm]
Pakethöhe	2.3 in [5.8 cm]
Versandgewicht (Verpackung)	13.9 oz [394.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 8 ft Heavy Duty 14 AWG Computer Power Cord - NEMA5-15P to C15
--------------------	---

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.