

8ft (2.4m) Heavy Duty Power Cord, NEMA 5-15P to C15 AC Power Cord, 15A 125V, 14AWG, Replacement Computer Power Cord, Monitor Power Cable, NEMA 5-15P to IEC 60320 C15 Power Cord - PC Power Supply Cable

Product ID: PXT515C158



The PXT515C158 8-foot Computer Power Cord features a C15 connector rated for high-temperature equipment, as well as 14 AWG wire suitable for high power connections - a reliable solution for connecting to NEMA 5-15P Power Distribution Units (PDU) located in switchgear rooms and data center environments, or large server applications that require a higher rated, heavier gauge cable.

Designed and constructed of high quality materials, this 5-15P to C15 power cable is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Compatible with Cisco, HP and other hardware devices with C15 power connections
- Connect large servers to PDUs, even in high-temperature environments

Features

- **HEAVY DUTY AC POWER CORD:** This 8ft (2.4m) 14AWG universal power cord with NEMA 5-15P and IEC 60320 C15 connectors is suitable for workstations/home office use. Rated to carry 125V at 15A.

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief connectors for durability Fire Rating: VW-1 3 Conductor Power Cable made with 100% Copper Wire This C15 thick gauge computer power cord is available in other lengths
- **SPECS:** 8ft (2.4m) AC Power Cord NEMA 5-15P to IEC 60320 C15 14AWG 125V 15A (Max) Jacket Type: SJT Jacket Material: PVC Black Temperature Range: 37F to 221F (3C to 105C) Cable Outer Diameter: 0.36in (9.1mm)
- **COMPATIBILITY:** PC Power Cord NEMA 5-15P works with North American outlets IEC C15 connector works with most servers and networking equipment Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 3-prong power cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - IEC 60320 C15 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	15 A

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	8.0 ft [2.4 m]
Product Length	8.0 ft [2.4 m]
Weight of Product	14.0 oz [396 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.2 cm]
Package Width	5.3 in [13.5 cm]
Package Height	2.3 in [5.8 cm]
Shipping (Package) Weight	13.9 oz [394.0 g]

What's in the Box

Included in Package	1 - 8 ft Heavy Duty 14 AWG Computer Power Cord - NEMA5-15P to C15
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***