

8ft (2.4m) Heavy Duty Power Cord, NEMA 5-15P to Right Angle C15, 15A 125V, 14AWG, Heavy Gauge PDU Power Cable, Replacement AC Power Cord, TAA Compliant, UL Listed

**Product ID:** PXT515C158RA



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

## Certifications, Reports and Compatibility



## Applications

- Connect a server or high-power rackmount equipment to a wall outlet or PDU

## Features

- **RIGHT ANGLE POWER CORD:** 8ft (2.44m) Heavy Duty Power Cable with NEMA 5-15P to Right Angle IEC 60320 C15 connector is suitable for servers or high-powered equipment; 90-degree C15 connectors facilitates access in tight spaces; Indoor use; Rated for 125V at 15A
- **BUILT FOR PERFORMANCE AND SAFETY:** Made with UL Listed components; VW-1 Fire Rated cable with fully-molded connector strain relief for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 8ft (2.44m); TAA Compliant; NEMA 5-15P to Right Angle IEC 60320 C15; 14AWG; 125V 15A (Max); Jacket Rating: SJT; Jacket Material: PVC; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.36in (9.3mm)
- **COMPATIBILITY:** NEMA 5-15P plug works with North American electrical outlets and PDUs; IEC C15 connector works with servers, switches, and high-power rackmount appliances; Replacement heavy gauge power cable
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This NEMA 5-15P to C15 power cord is available in other lengths

---

### Hardware

Warranty	Lifetime
Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

---

### Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - IEC 60320 C15 Power

---

### Power

Input Voltage	125V AC
Input Current	15A

---

**Environmental**

Operating Temperature	-20 to 105C (-4 to 221F)
Storage Temperature	-20 to 105C (-4 to 221F)
Humidity	0% to 65% RH

---

**Physical Characteristics**

Color	Black
Connector Style	Straight to Right Angle
Wire Gauge	14 AWG
Cable Length	8.0 ft [2.4 m]
Cable OD	0.4 in [9 mm]
Product Length	8.0 ft [2.4 m]
Product Width	2.4 in [6.2 cm]
Product Height	1.6 in [4.2 cm]
Weight of Product	14.0 oz [396.0 g]

---

**Packaging Information**

Package Length	11.4 in [29.0 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.6 in [4.0 cm]
Shipping (Package) Weight	14.3 oz [404.0 g]

---

**What's in the Box**

Included in Package	1 - 8ft (2.4m) 5-15P to Right Angle C15 Power Cord
---------------------	--

---

*\*Product appearance and specifications are subject to change without notice.*