

1m (3ft) Computer Power Cord, AS/NZS 3112 to C13, 10A 250V, 18AWG, Black Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable - UL Listed

Product ID: PXTA1011M



This high-quality power supply cord is designed to provide a durable, long-lasting connection to your peripheral devices.

The cord features one AS/NZS 3113 plug and one C13 connector, making it a suitable replacement for worn out or missing computer, monitor or printer power cords.

The PXTA1011M is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Plug your monitor, computer, or printer into a grounded power outlet
- Dependable replacement or spare computer power cord

Features

- **AC POWER CORD:** This 1m (3.3ft) 18AWG flexible laptop power cord with AS/NZS 3112 Plug and IEC 60320 C13 connectors is suitable for workstation/home office use. Rated to carry 250V at 10A.

- **PERFORMANCE AND SAFETY:** Fully molded strain relief on connectors for durability Fire Rating: VW-1 3 conductor Notebook Power Cable made from 100% copper wire CE Certified
- **SPECS:** 1m (3.3ft) Power Cable AS/NZS 3112 Plug to IEC 60320 C13 18AWG 250V 10A (Max) Jacket Rating: H05VV-F Jacket Material: PVC Color: Black Temperature Range: 14F to 140F (-10 to 60) Jacket Dimensions: 0.13x0.26in (3.5x6.8 mm)
- **COMPATIBILITY:** AC Power Cord AS/NZS 3112 Plug works with AUS / NZ outlets IEC 60320 C13 connector works with most power bricks for laptops/notebooks, monitors, scanners, printers, and more Replacement laptop power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this laptop charger cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

| | |
|----------------------|----------|
| Warranty | Lifetime |
| Number of Conductors | 3 |
| Cable Type | H05VV-F |

Connector(s)

| | |
|-------------|-----------------------------------|
| Connector A | 1 - AS/NZS 3112 Power (Australia) |
| Connector B | 1 - IEC 60320 C13 Power |

Power

| | |
|---------------|--------|
| Input Voltage | 250 AC |
| Input Current | 10 A |

Physical Characteristics

| | |
|-------------------|---------------------|
| Color | Black |
| Connector Style | Straight |
| Wire Gauge | 0.75mm ² |
| Cable Length | 3.3 ft [1 m] |
| Product Length | 3.3 ft [1.0 m] |
| Product Width | 1.6 in [4.1 cm] |
| Product Height | 1.6 in [4.1 cm] |
| Weight of Product | 4.6 oz [130.0 g] |

Packaging Information

| | |
|---------------------------|-------------------|
| Package Quantity | 1 |
| Package Length | 11.4 in [29.0 cm] |
| Package Width | 5.7 in [14.5 cm] |
| Package Height | 1.6 in [4.1 cm] |
| Shipping (Package) Weight | 4.7 oz [132.0 g] |

What's in the Box

| | |
|---------------------|-----------------------------------|
| Included in Package | 1 - AS/NZS 3112 to C13 power cord |
|---------------------|-----------------------------------|

Warranty Information

| | |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

**Product appearance and specifications are subject to change without notice.*