

15ft (4.5m) Power Extension Cord, C14 to C13 PDU Power Cord, 15A 250V, 14AWG, AC Power Cable for PDU/Power Supply, UL Listed

Produkt-ID: PXTC13C141415FNA



This certified C14 to C13 power extension cord extends connections from a PDU or UPS to servers, monitors, printers, and other IT equipment. The 15ft (4.5m) length provides extra reach, enabling flexible hardware placement in server rooms, network closets, and workstations.

Engineered to meet strict North American safety regulations, this power cord is UL Listed and adheres to the SJT designation for compliance with regional power standards. The VW-1 flame rating enhances fire safety, and is suitable for environments where fire resistance must be considered.

The 15ft (4.5m) length facilitates added distance between devices and power sources, allowing easier positioning of equipment without being limited by outlet locations.

Built for longevity, this C14 to C13 power extension cord features a fully molded design and is made from 100% copper wire. It is rated for 250V at 15A with 14AWG conductors, ensuring reliable and stable power transmission.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Establish a reliable power connection from your server to a PDU

Merkmale

- **UNIVERSAL EXTENSION CORD:** This C14 to C13 power extension cord allows you to extend connections from a PDU or UPS to servers, monitors, printers, and other IT or AV equipment; 15ft (4.5m) length provides extra reach for flexible equipment placement
- **DURABLE AND RELIABLE:** Extra-long (replacement) extension cord features a fully molded design and 100% copper wire for a secure and reliable connection; Rated for 250V at 15A with 14AWG conductors for safe and efficient operation
- **CERTIFIED FOR SAFETY:** UL Listed to meet North American safety regulations; SJT cable type ensures adherence to regional power standards, while the VW-1 fire rating enhances safety
- **SPECS:** 15-foot (4.5-meter) AC Power Cord; IEC 60320 C14 to IEC 60320 C13; UL Listed; Cable Type: SJT; 14AWG; 250V 15A (max); Jacket Material: PVC; Temp Range: 3°C to 60°C; Cable O.D.: 9.25mm (0.36in)
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this power extension cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Garantiebestimmungen	Lifetime
Typ der Kabelummantelung	PVC - Polyvinyl Chloride

Steckverbinder

Steckverbinder A	1 - IEC 60320 C13 Strom
Steckverbinder B	1 - IEC 60320 C14 Strom

Strom

Eingangsspannung	250 AC
Eingangsstrom	15A

Umgebungsbedingungen

Betriebstemperatur	0 to 70 (32°F to 158°F)
Lagertemperatur	-15 to 70 (5°F to 158°F)
Feuchtigkeit	30% - 90%

Physische

Eigenschaften

Farbe	Schwarz
Drahtstärke	14 AWG
Kabellänge	15.0 ft [4.6 m]
Außendurchmesser des Kabels	0.4 in [9.2 mm]
Produktlänge	180.7 in [4590 mm]
Produktbreite	1.1 in [28.7 mm]
Produkthöhe	0.8 in [20.9 mm]
Produktgewicht	23.7 oz [672 g]

Verpackungsinformationen

Paketlänge	10.0 in [25.5 cm]
Paketbreite	5.6 in [14.1 cm]
Pakethöhe	2.2 in [5.6 cm]
Versandgewicht (Verpackung)	1.5 lb [0.7 kg]

Verpackungsinhalt

Im Paket enthalten	1 - 4,5m C14 auf C13 Stromkabelverlängerung
--------------------	---

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.