

15ft (4.5m) Power Extension Cord, C14 to C13 PDU Power Cord, 15A 250V, 14AWG, AC Power Cable for PDU/Power Supply, UL Listed

Product ID: PXTC13C141415FNA



This certified C14 to C13 power extension cord extends connections from a PDU or UPS to servers, monitors, printers, and other IT equipment. The 15ft (4.5m) length provides extra reach, enabling flexible hardware placement in server rooms, network closets, and workstations.

Engineered to meet strict North American safety regulations, this power cord is UL Listed and adheres to the SJT designation for compliance with regional power standards. The VW-1 flame rating enhances fire safety, and is suitable for environments where fire resistance must be considered.

The 15ft (4.5m) length facilitates added distance between devices and power sources, allowing easier positioning of equipment without being limited by outlet locations.

Built for longevity, this C14 to C13 power extension cord features a fully molded design and is made from 100% copper wire. It is rated for 250V at 15A with 14AWG conductors, ensuring reliable and stable power transmission.

Certifications, Reports and Compatibility



Applications

- Establish a reliable power connection from your server to a PDU

Features

- **UNIVERSAL EXTENSION CORD:** This C14 to C13 power extension cord allows you to extend connections from a PDU or UPS to servers, monitors, printers, and other IT or AV equipment; 15ft (4.5m) length provides extra reach for flexible equipment placement
- **DURABLE AND RELIABLE:** Extra-long (replacement) extension cord features a fully molded design and 100% copper wire for a secure and reliable connection; Rated for 250V at 15A with 14AWG conductors for safe and efficient operation
- **CERTIFIED FOR SAFETY:** UL Listed to meet North American safety regulations; SJT cable type ensures adherence to regional power standards, while the VW-1 fire rating enhances safety
- **SPECS:** 15-foot (4.5-meter) AC Power Cord; IEC 60320 C14 to IEC 60320 C13; UL Listed; Cable Type: SJT; 14AWG; 250V 15A (max); Jacket Material: PVC; Temp Range: 3C to 60C; Cable O.D.: 9.25mm (0.36in)
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this power extension cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	1 - IEC 60320 C13 Power
Connector B	1 - IEC 60320 C14 Power

Power

Input Voltage	250 AC
Input Current	15A

Environmental

Operating Temperature	0 to 70 (32°F to 158°F)
Storage Temperature	-15 to 70 (5°F to 158°F)
Humidity	30% - 90%

Physical Characteristics

Color	Black
Wire Gauge	14 AWG

Cable Length	15.0 ft [4.6 m]
Cable OD	0.4 in [9.2 mm]
Product Length	180.7 in [4590 mm]
Product Width	1.1 in [28.7 mm]
Product Height	0.8 in [20.9 mm]
Weight of Product	23.7 oz [672 g]

Packaging Information

Package Length	11.4 in [29.0 cm]
Package Width	5.7 in [14.5 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	1.2 lb [0.5 kg]

What's in the Box

Included in Package	1 - 15ft C14 to C13 Power Extension Cord
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*