

3ft (1m) Heavy Duty Extension Cord, IEC 320 C14 to IEC 320 C15 Black Extension Cord, 15A 250V, 14AWG, Heavy Gauge Power Extension Cable, IEC 320 C14 to IEC 320 C15 AC Power Cord - UL Listed

**Product ID:** PXTC14C153



The PXTC14C153 C14 to C15 Power Cord (3 ft) features a C15 connector rated for high-temperature equipment, as well as 14 AWG wire suitable for high power connections - a reliable solution for connecting to C14 Power Distribution Units (PDU) located in switchgear rooms and data center environments, or large server applications that require a higher rated, heavier gauge cable.

Designed and constructed of high quality materials, this C14 to C15 power cable is backed by our Lifetime Warranty.

## Certifications, Reports and Compatibility



## Applications

- Connect large server applications to PDUs located in high-temperature environments
- Compatible with Cisco, HP and other hardware devices with C15 power connections

## Features

- **HEAVY DUTY EXTENSION CORD:** This 3ft (0.9m) 14AWG universal power cord with IEC 60320 C14 to IEC 60320 C15 connectors is suitable for workstations/home office Indoor use Rated to carry 250V at 15A

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief on connectors for durability  
Fire Rating: VW-1 3 Conductor Power cable made with 100% copper wire Available in other lengths
- **SPECS:** 3ft (0.9m) AC Power Cord IEC 60320 C14 to IEC 60320 C15 14AWG 250V 15A (Max) Jacket Type: SJT  
Jacket Material: PVC Black Temperature Range: 37F to 221F (3C to 105C) Cable Outer Diameter: 0.36in (9.14mm)
- **COMPATIBILITY:** PC Power Cord C14 to C13 works with most computer hardware Extend connections to servers, desktop computers, monitors, printers, and more Replacement power extension cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this power extension cable is backed for life, including free lifetime 24/5 multilingual technical assistance

---

#### Hardware

|                       |                          |
|-----------------------|--------------------------|
| Warranty              | Lifetime                 |
| Number of Conductors  | 3                        |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Cable Type            | SJT                      |

---

#### Connector(s)

|             |                         |
|-------------|-------------------------|
| Connector A | 1 - IEC 60320 C14 Power |
| Connector B | 1 - IEC 60320 C15 Power |

---

#### Power

|               |        |
|---------------|--------|
| Input Voltage | 250 AC |
| Input Current | 15 A   |

---

#### Environmental

|                       |                         |
|-----------------------|-------------------------|
| Operating Temperature | -20 to 60C (-4 to 140F) |
| Storage Temperature   | 0 to 30C ( 32 to 86F)   |
| Humidity              | <55%RH                  |

---

#### Physical Characteristics

|                |                   |
|----------------|-------------------|
| Color          | Black             |
| Wire Gauge     | 14 AWG            |
| Cable Length   | 3.0 ft [0.9 m]    |
| Product Length | 36.0 in [91.4 cm] |

|                   |                 |
|-------------------|-----------------|
| Product Width     | 1.1 in [2.8 cm] |
| Product Height    | 0.8 in [2.0 cm] |
| Weight of Product | 6.4 oz [181 g]  |

---

#### Packaging Information

|                           |                  |
|---------------------------|------------------|
| Package Quantity          | 1                |
| Package Length            | 3.2 in [8.1 cm]  |
| Package Width             | 7.9 in [20.0 cm] |
| Package Height            | 1.9 in [4.7 cm]  |
| Shipping (Package) Weight | 6.4 oz [180.0 g] |

---

#### What's in the Box

|                     |                                                 |
|---------------------|-------------------------------------------------|
| Included in Package | 1 - 3ft Computer Power Cord 14 AWG - C14 to C15 |
|---------------------|-------------------------------------------------|

---

#### Warranty Information

|          |          |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

---

***\*Product appearance and specifications are subject to change without notice.***