

6ft (1.8m) Heavy Duty Power Cord, C14 to C19, 15A 250V, 14AWG, Heavy Gauge PDU Power Cable, Replacement Server Power Cable, AC Power Cord, TAA Compliant, UL Listed

Produkt-ID: PXTc14C19146



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Connect high-power server equipment to a power outlet

Merkmale

- HEAVY DUTY POWER CORD: 6ft (1.8m) 14AWG Heavy Duty Power Cable with IEC 60320 C14 to IEC 60320 C19 connector is suitable for high-power rackmount equipment; Connect a server or switch to a power supply or PDU; Indoor use; Rated for 250V at 15A
- BUILT FOR PERFORMANCE AND SAFETY: Made with UL Listed components; VW-1 Fire Rated cable with fully-molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- SPECS: 6ft (1.8m); TAA Compliant; IEC 60320 C14 to IEC 60320 C19; 14AWG; 250V 15A (Max); Jacket Rating: SJT; Jacket Material: PVC; Color: Black; Temperature Range: -4°F to 221°F (-20 to 105); Cable O.D.: 0.36in (9.3mm)
- COMPATIBILITY: Heavy Duty Power Cord IEC C14 works with PDUs and power supplies; IEC C19 connector works with servers, switches, and rackmount appliances; Replacement heavy gauge PDU power cable
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Garantiebestimmungen Lifetime

Anzahl von Leitern 3

Steckverbinderplatten Nickel

Typ der PVC
Kabelummantelung

Feuerwiderstandsklass Klasse VW-1
e

Kabeltyp	SJT
<hr/>	
Steckverbinder	
Steckverbinder A	1 - IEC 60320 C14 Strom
Steckverbinder B	1 - IEC 60320 C19 Strom
<hr/>	
Strom	
Eingangsspannung	250V AC
Eingangsstrom	15A
<hr/>	
Umgebungsbedingungen	
Betriebstemperatur	-20° to 105°C (-4° to 221°F)
Lagertemperatur	-20° to 105°C (-4° to 221°F)
Feuchtigkeit	0% to 65% RH
<hr/>	
Physische Eigenschaften	
Farbe	Schwarz
Steckverbinderart	Gerade
Drahtstärke	14 AWG
Kabellänge	6.0 ft [1.8 m]
Außendurchmesser des Kabels	0.4 in [9.3 mm]
Produktlänge	6.0 ft [1.8 m]
Produktbreite	1.1 in [2.9 cm]
Produkthöhe	0.9 in [2.3 cm]
Produktgewicht	11.1 oz [315.0 g]
<hr/>	
Verpackungsinformationen	
Paketlänge	10.6 in [27.0 cm]
Paketbreite	4.4 in [11.3 cm]

Pakethöhe 1.7 in [4.3 cm]

Versandgewicht 11.7 oz [332.0 g]
(Verpackung)

Verpackungsinhalt

Im Paket enthalten 1 - 1,8m C14 zu C19 Hochbelastbares Stromkabel

Garantieinformatio
nen

Warranty Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.