

6ft (1.8m) Heavy Duty Power Cord, C14 to C19, 15A 250V, 14AWG, Heavy Gauge PDU Power Cable, Replacement Server Power Cable, AC Power Cord, TAA Compliant, UL Listed

Product ID: PXTC14C19146



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Certifications, Reports and Compatibility



Applications

- Connect high-power server equipment to a power outlet

Features

- **HEAVY DUTY POWER CORD:** 6ft (1.8m) 14AWG Heavy Duty Power Cable with IEC 60320 C14 to IEC 60320 C19 connector is suitable for high-power rackmount equipment; Connect a server or switch to a power supply or PDU; Indoor use; Rated for 250V at 15A
- **BUILT FOR PERFORMANCE AND SAFETY:** Made with UL Listed components; VW-1 Fire Rated cable with fully-molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 6ft (1.8m); TAA Compliant; IEC 60320 C14 to IEC 60320 C19; 14AWG; 250V 15A (Max); Jacket Rating: SJT; Jacket Material: PVC; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.36in (9.3mm)
- **COMPATIBILITY:** Heavy Duty Power Cord IEC C14 works with PDUs and power supplies; IEC C19 connector works with servers, switches, and rackmount appliances; Replacement heavy gauge PDU power cable
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

Connector(s)

Connector A	1 - IEC 60320 C14 Power
Connector B	1 - IEC 60320 C19 Power

Power

Input Voltage	250V AC
---------------	---------

	Input Current	15A
Environmental		
	Operating Temperature	-20 to 105C (-4 to 221F)
	Storage Temperature	-20 to 105C (-4 to 221F)
	Humidity	0% to 65% RH
Physical Characteristics		
	Color	Black
	Connector Style	Straight
	Wire Gauge	14 AWG
	Cable Length	6.0 ft [1.8 m]
	Cable OD	0.4 in [9.3 mm]
	Product Length	6.0 ft [1.8 m]
	Product Width	1.1 in [2.9 cm]
	Product Height	0.9 in [2.3 cm]
	Weight of Product	11.1 oz [315.0 g]
Packaging Information		
	Package Length	10.6 in [27.0 cm]
	Package Width	4.4 in [11.3 cm]
	Package Height	1.7 in [4.3 cm]
	Shipping (Package) Weight	11.7 oz [332.0 g]
What's in the Box		
	Included in Package	1 - 6ft C14 to C19 Heavy Duty Power Cord
Warranty Information		
	Warranty	Lifetime

****Product appearance and specifications are subject to change without notice.***