

Computer Power Cord - C19 to C20, 14 AWG, 3 ft

Product ID: PXTC19C20143



This C19 to C20 power cord from StarTech.com features 14 AWG wire that's suitable for high power connections, making it perfect for server application and connecting to a Power Distribution Unit (PDU).

Plus, you can use the cable to extend the reach of your existing power cord by 3 feet, which gives you the extra distance you need to place your devices according to your server room configuration.

Expertly designed and constructed of high-quality materials, the PXTC19C20143 power cord is backed by our lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Connect your server to a PDU
- Extend the connection between your server and PDU by up to 3 feet

Features

- Rated to carry 250V at 15A
- 14 AWG wire

- UL, RoHS compliant

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	1 - IEC 60320 C19 Power
Connector B	1 - IEC 60320 C20 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	250 AC
Input Current	15 A

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	3.0 ft [0.9 m]
Product Length	36.0 in [91.4 cm]
Weight of Product	8.0 oz [228 g]

Packaging Information

Package Quantity	1
Package Length	9.8 in [25.0 cm]
Package Width	3.0 in [7.7 cm]
Package Height	2.3 in [5.9 cm]

Shipping (Package) Weight	7.4 oz [210.0 g]
------------------------------	------------------

What's in the Box

Included in Package	1 - 3 ft 14 AWG Computer Power Cord - C19 to C20
---------------------	--

**Warranty
Information**

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*