

6ft (1.8m) Computer Power Cord, Flat NEMA 5-15P to C13, 10A 125V, 18AWG, Black
Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor
Power Cable - UL Listed

Produkt-ID: PXTF1016



This NEMA 5-15P to C13 power cord features a flat low-profile plug that sits flush against the outlet on your power strip, surge protector or wall outlet. The flush connection saves space and helps to avoid blocking other open outlets.

The power supply cord is constructed of top quality materials, and designed to provide a durable, long-lasting connection to your peripheral devices. It makes a suitable replacement for worn out or missing computer, monitor or printer power cords.

The PXTF1016 is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Plug your monitor, computer, or printer into a grounded power outlet
- Dependable replacement or spare computer power cord

Merkmale

- **AC POWER CORD:** This 6ft (1.8m) 18AWG flexible computer power cable with Flat NEMA 5-15P and IEC 60320 C13 connectors is suitable for workstation/home office use | Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief connectors for durability | 3 Conductor Power Cable made from 100% Copper Wire | Fire Rating: VW-1
- **SPECS:** 6ft (1.8m) Power Cable | Flat NEMA 5-15P to IEC 60320 C13 | 18AWG | 125V 10A (Max) | Jacket Rating: SVT | Jacket Material: PVC | Color: Black | Temperature Range: 37°F to 140°F (3 to 60) | Cable Outer Diameter: 0.25in (6.4mm)
- **COMPATIBILITY:** Flat NEMA 5-15P works with North American electrical outlets | IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more | Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance | This C13 power cord is available in other lengths

Hardware

Garantiebestimmungen Lifetime

Anzahl von Leitern 3

Kabeltyp SVT

Steckverbinder

Steckverbinder A 1 - NEMA 5-15 Strom (Nordamerika)

1 - IEC 60320 C13 Strom

Spezielle Hinweise/Anforderungen

Hinweis UL Listed

Strom

Eingangsspannung 125 AC

Eingangsstrom 10 A

Physische Eigenschaften

Farbe Schwarz

Steckverbinderart	Flat to Straight
Drahtstärke	18 AWG
Kabellänge	6.0 ft [1.8 m]
Produktlänge	6.0 ft [1.8 m]
Produktbreite	1.0 in [2.6 cm]
Produkthöhe	1.6 in [4.1 cm]
Produktgewicht	5.4 oz [153.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	11.0 in [28.0 cm]
Paketbreite	5.3 in [13.5 cm]
Pakethöhe	1.0 in [25.0 mm]
Versandgewicht (Verpackung)	5.6 oz [159.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - NEMA 5-15P to C13 power cord
--------------------	----------------------------------

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.