

6ft (1.8m) Computer Power Cord, Flat NEMA 5-15P to C13, 10A 125V, 18AWG, Black Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable - UL Listed

Product ID: PXTF1016



This NEMA 5-15P to C13 power cord features a flat low-profile plug that sits flush against the outlet on your power strip, surge protector or wall outlet. The flush connection saves space and helps to avoid blocking other open outlets.

The power supply cord is constructed of top quality materials, and designed to provide a durable, long-lasting connection to your peripheral devices. It makes a suitable replacement for worn out or missing computer, monitor or printer power cords.

The PXTF1016 is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Plug your monitor, computer, or printer into a grounded power outlet
- Dependable replacement or spare computer power cord

Features

- **AC POWER CORD:** This 6ft (1.8m) 18AWG flexible computer power cable with Flat NEMA 5-15P and IEC 60320 C13 connectors is suitable for workstation/home office use. Rated to carry 125V at 10A.

• **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief connectors for durability 3 Conductor Power Cable made from 100% Copper Wire Fire Rating: VW-1

• **SPECS:** 6ft (1.8m) Power Cable Flat NEMA 5-15P to IEC 60320 C13 18AWG 125V 10A (Max) Jacket Rating: SVT Jacket Material: PVC Color: Black Temperature Range: 37F to 140F (3 to 60) Cable Outer Diameter: 0.25in (6.4mm)

• **COMPATIBILITY:** Flat NEMA 5-15P works with North American electrical outlets IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more Replacement PC power supply cable/cord

• **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance This C13 power cord is available in other lengths

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Type	SVT

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
	1 - IEC 60320 C13 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	10 A

Physical Characteristics

Color	Black
Connector Style	Flat to Straight
Wire Gauge	18 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]

Product Width	1.0 in [2.6 cm]
Product Height	1.6 in [4.1 cm]
Weight of Product	5.4 oz [153.0 g]

Packaging Information

Package Quantity	1
Package Length	11.0 in [28.0 cm]
Package Width	5.3 in [13.5 cm]
Package Height	1.0 in [25.0 mm]
Shipping (Package) Weight	5.6 oz [159.0 g]

What's in the Box

Included in Package	1 - NEMA 5-15P to C13 power cord
---------------------	----------------------------------

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***