

3ft (1m) Hospital Grade Power Cord, 18AWG, NEMA 5-15P to C13, 10A 125V, Green Dot Medical Power Cable, PC Power Supply Power Cable, Printer / Monitor Power Cable - UL Listed

Product ID: PXTMG1013



This NEMA 5-15P to C13 power cord features a hospital-grade plug that lets you connect your computer, monitor or other lab equipment to a hospital-grade AC power outlet.

The NEMA 5-15P-HG plug has been tested to UL and CSA standards in order to protect patients and medical staff against faulty ground connections that can be caused by frequent and abrupt connects and disconnects.

The power cord is built to withstand the demands of a hospital environment and is a dependable and safe replacement for worn out or missing power cords.

The PXTMG1013 is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Plug your computer, monitor and other medical equipment with a C14 port to a hospital-grade AC power outlet

Features

- **HOSPITAL GRADE POWER CORD:** This 3ft (0.9m) 18AWG hospital grade power cord with NEMA 5-15P and IEC 60320 C13 connectors is safe for hospital and medical environments. Rated to carry 125V at 10A

- **PERFORMANCE AND SAFETY:** UL Listed Tested to UL62, UL817 and CAN/CSA C22.2 no. 21-14 Fully molded strain relief connectors for durability 3 Conductor Power Cable made with 100% Copper Wire Fire Rating: VW-1
- **SPECS:** 3ft (0.9m) Power Cable NEMA 5-15P to IEC 60320 C13 18AWG 125V 10A (Max) Jacket Rating: SVT Jacket Material: PVC Color: Black Temperature Range: 37F to 140F (3 to 60) Cable Outer Diameter: 0.25in (6.4mm)
- **COMPATIBILITY:** NEMA 5-15P hospital grade plug works with North American electrical outlets IEC C13 connector works with most computers, monitors and TVs Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Type	SVT

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - IEC 60320 C13 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	10 A

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	18 AWG
Cable Length	3.0 ft [0.9 m]
Product Length	36.0 in [91.4 cm]
Product Width	1.3 in [3.2 cm]

Product Height	1.3 in [3.2 cm]
Weight of Product	4.1 oz [116.0 g]

Packaging Information

Package Quantity	1
Package Length	7.4 in [18.7 cm]
Package Width	2.9 in [7.4 cm]
Package Height	1.6 in [4.1 cm]
Shipping (Package) Weight	4.4 oz [124.0 g]

What's in the Box

Included in Package	1 - NEMA 5-15P to C13 power cord
---------------------	----------------------------------

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***